

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581731

Luminaire Tested: **HCC6S15D010SL-HM60525835-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581731
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010SL-HM60525835-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1708.6 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581731
CATALOG NUMBER: HCC6S15D010SL-HM60525835-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P581731

CATALOG NUMBER: HCC6S15D010SL-HM60525835-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81134
5°	82401
10°	87095
15°	96970
20°	100564
25°	82517
30°	57813
35°	39444
40°	20553
45°	7226
50°	3232
55°	1032
60°	592
65°	428
70°	353
75°	233
80°	0
85°	0



TEST NUMBER: P581731
 CATALOG NUMBER: HCC6S15D010SL-HM60525835-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	8.5
10°-20°	480.5	28.1
20°-30°	611.9	35.8
30°-40°	364.7	21.3
40°-50°	88.4	5.2
50°-60°	13.5	0.8
60°-70°	3.4	0.2
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1237.4	72.4
0°-40°	1602.1	93.8
0°-60°	1704.1	99.7
0°-90°	1708.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1708.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1480	
5°	1497	145
15°	1709	481
25°	1364	612
35°	589	365
45°	93	88
55°	11	14
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581731
CATALOG NUMBER: HCC6S15D010SL-HM60525835-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	1480.0
2.5°	1480.0
5°	1497.4
7.5°	1524.5
10°	1564.6
12.5°	1627.4
15°	1708.6
17.5°	1759.6
20°	1723.8
22.5°	1586.3
25°	1364.2
27.5°	1119.2
30°	913.3
32.5°	746.5
35°	589.4
37.5°	434.5
40°	287.2
42.5°	154.9
45°	93.2
47.5°	58.5
50°	37.9
52.5°	22.7
55°	10.8
57.5°	6.5
60°	5.4
62.5°	4.3
65°	3.3
67.5°	2.2
70°	2.2
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)