

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581743

Luminaire Tested: **HCC6S15D010BZ-HM60525835-61WDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581743  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S15D010BZ-HM60525835-61WDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1581.8 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581743  
CATALOG NUMBER: HCC6S15D010BZ-HM60525835-61WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581743

CATALOG NUMBER: HCC6S15D010BZ-HM60525835-61WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	53981
5°	53945
10°	53428
15°	52872
20°	51373
25°	49213
30°	45665
35°	39291
40°	28682
45°	19645
50°	15795
55°	13763
60°	12707
65°	12089
70°	11284
75°	10548
80°	9566
85°	8240



TEST NUMBER: P581743  
 CATALOG NUMBER: HCC6S15D010BZ-HM60525835-61WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.9	5.9
10°-20°	261.6	16.5
20°-30°	372.1	23.5
30°-40°	358.2	22.6
40°-50°	206.1	13.0
50°-60°	130.6	8.3
60°-70°	92.5	5.8
70°-80°	52.7	3.3
80°-90°	15.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	726.7	45.9
0°-40°	1084.9	68.6
0°-60°	1421.6	89.9
0°-90°	1581.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1581.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	985	
5°	980	93
15°	932	262
25°	814	372
35°	587	358
45°	253	206
55°	144	131
65°	93	92
75°	50	53
85°	13	15
90°	0	



TEST NUMBER: P581743  
CATALOG NUMBER: HCC6S15D010BZ-HM60525835-61WDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	984.7
2.5°	980.3
5°	980.3
7.5°	973.8
10°	959.8
12.5°	945.7
15°	931.6
17.5°	909.9
20°	880.6
22.5°	848.2
25°	813.6
27.5°	771.2
30°	721.4
32.5°	660.8
35°	587.1
37.5°	497.2
40°	400.8
42.5°	316.3
45°	253.4
47.5°	213.4
50°	185.2
52.5°	162.5
55°	144.0
57.5°	127.8
60°	115.9
62.5°	105.1
65°	93.2
67.5°	82.3
70°	70.4
72.5°	59.6
75°	49.8
77.5°	40.1
80°	30.3
82.5°	21.7
85°	13.1
87.5°	5.4
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)