

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581737

Luminaire Tested: **HCC6W15D010SL-HM60525835-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010SL-HM60525835-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1534.1 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581737
CATALOG NUMBER: HCC6W15D010SL-HM60525835-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P581737
 CATALOG NUMBER: HCC6W15D010SL-HM60525835-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90		88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80		78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71		69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64		62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58		56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53		51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48		46
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44		43
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41		39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38		36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54837
5°	54688
10°	53868
15°	53014
20°	51268
25°	48831
30°	44589
35°	35898
40°	24195
45°	17645
50°	15249
55°	13773
60°	13069
65°	12362
70°	11637
75°	11014
80°	10260
85°	9561



TEST NUMBER: P581737
 CATALOG NUMBER: HCC6W15D010SL-HM60525835-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	6.1
10°-20°	262.3	17.1
20°-30°	368.6	24.0
30°-40°	328.1	21.4
40°-50°	183.3	12.0
50°-60°	130.6	8.5
60°-70°	95.0	6.2
70°-80°	55.0	3.6
80°-90°	17.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	724.9	47.3
0°-40°	1053.0	68.6
0°-60°	1367.0	89.1
0°-90°	1534.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1534.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1000	
5°	994	94
15°	934	262
25°	807	369
35°	536	328
45°	228	183
55°	144	131
65°	95	95
75°	52	55
85°	15	17
90°	0	



TEST NUMBER: P581737
CATALOG NUMBER: HCC6W15D010SL-HM60525835-61PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1000.3
2.5°	996.0
5°	993.8
7.5°	985.1
10°	967.7
12.5°	951.5
15°	934.1
17.5°	910.3
20°	878.8
22.5°	844.2
25°	807.3
27.5°	761.8
30°	704.4
32.5°	630.7
35°	536.4
37.5°	430.3
40°	338.1
42.5°	269.8
45°	227.6
47.5°	199.4
50°	178.8
52.5°	160.4
55°	144.1
57.5°	131.1
60°	119.2
62.5°	108.4
65°	95.3
67.5°	84.6
70°	72.6
72.5°	61.7
75°	52.0
77.5°	42.2
80°	32.5
82.5°	23.8
85°	15.2
87.5°	7.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)