

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581755

Luminaire Tested: **HCC6W15D010MB-HM60525840-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010MB-HM60525840-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1583.6 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581755
CATALOG NUMBER: HCC6W15D010MB-HM60525840-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P581755

CATALOG NUMBER: HCC6W15D010MB-HM60525840-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78		
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69		
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62		
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56		
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51		
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43		
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39		
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56602
5°	56444
10°	55605
15°	54722
20°	52925
25°	50404
30°	46026
35°	37055
40°	24975
45°	18211
50°	15744
55°	14222
60°	13486
65°	12764
70°	12005
75°	11374
80°	10607
85°	9875



TEST NUMBER: P581755
 CATALOG NUMBER: HCC6W15D010MB-HM60525840-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.1	6.1
10°-20°	270.8	17.1
20°-30°	380.4	24.0
30°-40°	338.6	21.4
40°-50°	189.2	12.0
50°-60°	134.9	8.5
60°-70°	98.1	6.2
70°-80°	56.8	3.6
80°-90°	17.7	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	748.3	47.3
0°-40°	1086.9	68.6
0°-60°	1411.0	89.1
0°-90°	1583.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1583.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1032	
5°	1026	97
15°	964	271
25°	833	380
35°	554	339
45°	235	189
55°	149	135
65°	98	98
75°	54	57
85°	16	18
90°	0	



TEST NUMBER: P581755
CATALOG NUMBER: HCC6W15D010MB-HM60525840-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1032.5
2.5°	1028.0
5°	1025.7
7.5°	1016.8
10°	998.9
12.5°	982.1
15°	964.2
17.5°	939.7
20°	907.2
22.5°	871.3
25°	833.3
27.5°	786.3
30°	727.1
32.5°	651.0
35°	553.7
37.5°	444.1
40°	349.0
42.5°	278.5
45°	234.9
47.5°	205.8
50°	184.6
52.5°	165.6
55°	148.8
57.5°	135.4
60°	123.0
62.5°	111.9
65°	98.4
67.5°	87.3
70°	74.9
72.5°	63.8
75°	53.7
77.5°	43.6
80°	33.6
82.5°	24.6
85°	15.7
87.5°	7.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)