

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593092

Luminaire Tested: **HCC6W15D010SL-HM60525850-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010SL-HM60525850-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1654.0 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593092
CATALOG NUMBER: HCC6W15D010SL-HM60525850-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P593092
 CATALOG NUMBER: HCC6W15D010SL-HM60525850-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84			84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77			77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59			59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54			54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50			50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64776
5°	65205
10°	65958
15°	67316
20°	67696
25°	65586
30°	59496
35°	48379
40°	32110
45°	17870
50°	10021
55°	5563
60°	3059
65°	2322
70°	1619
75°	1186
80°	726
85°	692



TEST NUMBER: P593092
 CATALOG NUMBER: HCC6W15D010SL-HM60525850-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	6.8
10°-20°	334.4	20.2
20°-30°	492.9	29.8
30°-40°	440.9	26.7
40°-50°	191.3	11.6
50°-60°	56.2	3.4
60°-70°	17.9	1.1
70°-80°	6.3	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.5	56.9
0°-40°	1381.4	83.5
0°-60°	1628.8	98.5
0°-90°	1654.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1654.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1182	
5°	1185	113
15°	1186	334
25°	1084	493
35°	723	441
45°	230	191
55°	58	56
65°	18	18
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P593092
CATALOG NUMBER: HCC6W15D010SL-HM60525850-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1181.6
2.5°	1178.2
5°	1184.9
7.5°	1187.2
10°	1184.9
12.5°	1184.9
15°	1186.1
17.5°	1179.4
20°	1160.4
22.5°	1128.0
25°	1084.3
27.5°	1022.7
30°	939.9
32.5°	841.5
35°	722.9
37.5°	587.5
40°	448.7
42.5°	327.9
45°	230.5
47.5°	164.5
50°	117.5
52.5°	83.9
55°	58.2
57.5°	39.2
60°	27.9
62.5°	22.4
65°	17.9
67.5°	13.4
70°	10.1
72.5°	7.8
75°	5.6
77.5°	4.4
80°	2.3
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)