

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581773

Luminaire Tested: **HCC6S15D010SL-HM60525927-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010SL-HM60525927-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1185.7 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581773
CATALOG NUMBER: HCC6S15D010SL-HM60525927-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P581773

CATALOG NUMBER: HCC6S15D010SL-HM60525927-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43				
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39				
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42376
5°	42268
10°	41632
15°	40976
20°	39623
25°	37738
30°	34455
35°	27746
40°	18699
45°	13637
50°	11786
55°	10638
60°	10109
65°	9560
70°	8992
75°	8515
80°	7924
85°	7359



TEST NUMBER: P581773
 CATALOG NUMBER: HCC6S15D010SL-HM60525927-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.7	6.1
10°-20°	202.7	17.1
20°-30°	284.8	24.0
30°-40°	253.5	21.4
40°-50°	141.7	12.0
50°-60°	100.9	8.5
60°-70°	73.5	6.2
70°-80°	42.5	3.6
80°-90°	13.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.2	47.3
0°-40°	813.8	68.6
0°-60°	1056.4	89.1
0°-90°	1185.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1185.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	773	
5°	768	73
15°	722	203
25°	624	285
35°	415	254
45°	176	142
55°	111	101
65°	74	73
75°	40	43
85°	12	13
90°	0	



TEST NUMBER: P581773
CATALOG NUMBER: HCC6S15D010SL-HM60525927-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	773.0
2.5°	769.6
5°	768.1
7.5°	761.4
10°	747.9
12.5°	735.4
15°	722.0
17.5°	703.5
20°	679.2
22.5°	652.4
25°	623.9
27.5°	588.7
30°	544.3
32.5°	487.5
35°	414.6
37.5°	332.4
40°	261.3
42.5°	208.5
45°	175.9
47.5°	154.1
50°	138.2
52.5°	123.9
55°	111.3
57.5°	101.4
60°	92.2
62.5°	83.8
65°	73.7
67.5°	65.4
70°	56.1
72.5°	47.8
75°	40.2
77.5°	32.7
80°	25.1
82.5°	18.4
85°	11.7
87.5°	5.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)