

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581779

Luminaire Tested: **HCC6W15D010MW-HM60525927-61WDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581779  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W15D010MW-HM60525927-61WDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1222.5 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581779  
CATALOG NUMBER: HCC6W15D010MW-HM60525927-61WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581779  
 CATALOG NUMBER: HCC6W15D010MW-HM60525927-61WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78				
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69				
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56				
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51				
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42				
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39				
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	41718
5°	41690
10°	41287
15°	40857
20°	39711
25°	38028
30°	35290
35°	30370
40°	22163
45°	15188
50°	12204
55°	10638
60°	9824
65°	9340
70°	8719
75°	8155
80°	7419
85°	6353



TEST NUMBER: P581779  
 CATALOG NUMBER: HCC6W15D010MW-HM60525927-61WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.8	5.9
10°-20°	202.2	16.5
20°-30°	287.6	23.5
30°-40°	276.9	22.6
40°-50°	159.3	13.0
50°-60°	100.9	8.3
60°-70°	71.5	5.8
70°-80°	40.8	3.3
80°-90°	11.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.6	45.9
0°-40°	838.4	68.6
0°-60°	1098.6	89.9
0°-90°	1222.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1222.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	761	
5°	758	72
15°	720	202
25°	629	288
35°	454	277
45°	196	159
55°	111	101
65°	72	71
75°	38	41
85°	10	12
90°	0	



TEST NUMBER: P581779  
CATALOG NUMBER: HCC6W15D010MW-HM60525927-61WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	761.0
2.5°	757.6
5°	757.6
7.5°	752.6
10°	741.7
12.5°	730.8
15°	719.9
17.5°	703.2
20°	680.7
22.5°	655.5
25°	628.7
27.5°	596.1
30°	557.5
32.5°	510.6
35°	453.8
37.5°	384.3
40°	309.7
42.5°	244.5
45°	195.9
47.5°	164.9
50°	143.1
52.5°	125.5
55°	111.3
57.5°	98.7
60°	89.6
62.5°	81.2
65°	72.0
67.5°	63.7
70°	54.4
72.5°	46.1
75°	38.5
77.5°	31.0
80°	23.5
82.5°	16.8
85°	10.1
87.5°	4.2
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)