

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581795

Luminaire Tested: **HCC6S15D010SL-HM60525930-61WDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010SL-HM60525930-61WDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1474.3 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581795
CATALOG NUMBER: HCC6S15D010SL-HM60525930-61WDC

Luminous Intensity Polar Plot





TEST NUMBER: P581795

CATALOG NUMBER: HCC6S15D010SL-HM60525930-61WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56	56	56	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52	52	52	52
9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48	48	48	48
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52271
5°	52971
10°	54959
15°	59773
20°	66821
25°	70335
30°	61915
35°	42945
40°	25641
45°	12187
50°	4597
55°	1921
60°	592
65°	467
70°	289
75°	191
80°	284
85°	0



TEST NUMBER: P581795
 CATALOG NUMBER: HCC6S15D010SL-HM60525930-61WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	6.3
10°-20°	302.4	20.5
20°-30°	518.2	35.1
30°-40°	402.4	27.3
40°-50°	133.0	9.0
50°-60°	20.4	1.4
60°-70°	3.6	0.2
70°-80°	1.3	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	913.2	61.9
0°-40°	1315.6	89.2
0°-60°	1469.0	99.6
0°-90°	1474.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1474.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	954	
5°	963	93
15°	1053	302
25°	1163	518
35°	642	402
45°	157	133
55°	20	20
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581795
CATALOG NUMBER: HCC6S15D010SL-HM60525930-61WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	953.5
2.5°	952.6
5°	962.6
7.5°	973.6
10°	987.3
12.5°	1014.7
15°	1053.2
17.5°	1099.8
20°	1145.4
22.5°	1172.0
25°	1162.8
27.5°	1099.8
30°	978.1
32.5°	814.6
35°	641.7
37.5°	487.3
40°	358.3
42.5°	253.2
45°	157.2
47.5°	87.7
50°	53.9
52.5°	32.9
55°	20.1
57.5°	10.1
60°	5.4
62.5°	4.5
65°	3.6
67.5°	2.7
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)