

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581812

Luminaire Tested: **HCC6W15D010MB-HM60525935-61WDBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010MB-HM60525935-61WDBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1270.1 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581812
CATALOG NUMBER: HCC6W15D010MB-HM60525935-61WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P581812
 CATALOG NUMBER: HCC6W15D010MB-HM60525935-61WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94	92
2	107	101	97	93	104	100	95	92	96	93	90		93	91	88		90	88	86	85
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74		81	77	73		79	75	72	71
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		73	69	66	65
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	57	77	68	61	57	66	61	57		65	60	56		64	59	56	54
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60	55	52	50
9	70	59	53	48	69	59	53	48	58	52	48		57	52	48		56	51	48	46
10	66	56	49	45	65	55	49	45	54	49	45		53	48	44		53	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45112
5°	45443
10°	46236
15°	48065
20°	50084
25°	51868
30°	51179
35°	42643
40°	27337
45°	13660
50°	5424
55°	1845
60°	526
65°	363
70°	305
75°	402
80°	284
85°	0



TEST NUMBER: P581812
 CATALOG NUMBER: HCC6W15D010MB-HM60525935-61WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.0	6.2
10°-20°	240.2	18.9
20°-30°	392.2	30.9
30°-40°	384.5	30.3
40°-50°	147.4	11.6
50°-60°	21.6	1.7
60°-70°	3.2	0.2
70°-80°	1.6	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.4	56.0
0°-40°	1095.9	86.3
0°-60°	1265.0	99.6
0°-90°	1270.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1270.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	823	
5°	826	79
15°	847	240
25°	858	392
35°	637	385
45°	176	147
55°	19	22
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P581812
CATALOG NUMBER: HCC6W15D010MB-HM60525935-61WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	822.9
2.5°	820.9
5°	825.8
7.5°	828.7
10°	830.6
12.5°	837.3
15°	846.9
17.5°	854.7
20°	858.5
22.5°	859.4
25°	857.5
27.5°	844.1
30°	808.5
32.5°	741.0
35°	637.2
37.5°	509.2
40°	382.0
42.5°	272.4
45°	176.2
47.5°	107.8
50°	63.6
52.5°	36.5
55°	19.3
57.5°	8.6
60°	4.8
62.5°	3.9
65°	2.8
67.5°	2.8
70°	1.9
72.5°	1.9
75°	1.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)