

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581805

Luminaire Tested: **HCC6S15D010MB-HM60525935-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010MB-HM60525935-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1328.9 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581805
CATALOG NUMBER: HCC6S15D010MB-HM60525935-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581805

CATALOG NUMBER: HCC6S15D010MB-HM60525935-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49470
5°	49284
10°	48468
15°	47611
20°	45965
25°	43587
30°	39645
35°	31675
40°	21132
45°	15064
50°	12554
55°	10943
60°	10339
65°	9729
70°	8944
75°	8366
80°	7608
85°	6667



TEST NUMBER: P581805
 CATALOG NUMBER: HCC6S15D010MB-HM60525935-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.7	6.4
10°-20°	235.5	17.7
20°-30°	329.2	24.8
30°-40°	290.0	21.8
40°-50°	156.6	11.8
50°-60°	104.7	7.9
60°-70°	74.2	5.6
70°-80°	41.8	3.1
80°-90°	12.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	649.4	48.9
0°-40°	939.4	70.7
0°-60°	1200.7	90.4
0°-90°	1328.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1328.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	902	
5°	896	85
15°	839	236
25°	721	329
35°	473	290
45°	194	157
55°	114	105
65°	75	74
75°	40	42
85°	11	12
90°	0	



TEST NUMBER: P581805
CATALOG NUMBER: HCC6S15D010MB-HM60525935-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	902.4
2.5°	897.6
5°	895.6
7.5°	887.0
10°	870.7
12.5°	855.2
15°	838.9
17.5°	816.7
20°	787.9
22.5°	756.1
25°	720.6
27.5°	679.2
30°	626.3
32.5°	560.9
35°	473.3
37.5°	378.1
40°	295.3
42.5°	232.8
45°	194.3
47.5°	168.3
50°	147.2
52.5°	129.8
55°	114.5
57.5°	103.9
60°	94.3
62.5°	84.7
65°	75.0
67.5°	65.4
70°	55.8
72.5°	47.1
75°	39.5
77.5°	31.8
80°	24.1
82.5°	17.4
85°	10.6
87.5°	4.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)