

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581826

Luminaire Tested: **HCC6S15D010MB-HM60525940-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010MB-HM60525940-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1326.1 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581826
CATALOG NUMBER: HCC6S15D010MB-HM60525940-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P581826

CATALOG NUMBER: HCC6S15D010MB-HM60525940-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50226
5°	49994
10°	48880
15°	47736
20°	45947
25°	43448
30°	39487
35°	31962
40°	21555
45°	14808
50°	12136
55°	10618
60°	10043
65°	9482
70°	8896
75°	8472
80°	7703
85°	6730



TEST NUMBER: P581826
 CATALOG NUMBER: HCC6S15D010MB-HM60525940-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	6.5
10°-20°	236.2	17.8
20°-30°	328.2	24.7
30°-40°	292.2	22.0
40°-50°	155.1	11.7
50°-60°	101.4	7.6
60°-70°	72.7	5.5
70°-80°	42.2	3.2
80°-90°	12.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	650.2	49.0
0°-40°	942.4	71.1
0°-60°	1198.9	90.4
0°-90°	1326.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1326.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	916	
5°	908	86
15°	841	236
25°	718	328
35°	478	292
45°	191	155
55°	111	101
65°	73	73
75°	40	42
85°	11	12
90°	0	



TEST NUMBER: P581826
CATALOG NUMBER: HCC6S15D010MB-HM60525940-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	916.2
2.5°	911.3
5°	908.5
7.5°	897.7
10°	878.1
12.5°	860.7
15°	841.1
17.5°	816.7
20°	787.6
22.5°	754.4
25°	718.3
27.5°	676.5
30°	623.8
32.5°	560.5
35°	477.6
37.5°	386.0
40°	301.2
42.5°	233.9
45°	191.0
47.5°	162.8
50°	142.3
52.5°	125.8
55°	111.1
57.5°	100.4
60°	91.6
62.5°	82.9
65°	73.1
67.5°	64.4
70°	55.5
72.5°	47.8
75°	40.0
77.5°	32.1
80°	24.4
82.5°	17.6
85°	10.7
87.5°	4.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)