

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581827

Luminaire Tested: **HCC6S15D010MB-HM60525940-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010MB-HM60525940-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1379.7 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581827
CATALOG NUMBER: HCC6S15D010MB-HM60525940-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P581827
 CATALOG NUMBER: HCC6S15D010MB-HM60525940-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49311
5°	49180
10°	48446
15°	47679
20°	46111
25°	43920
30°	40095
35°	32284
40°	21762
45°	15862
50°	13714
55°	12387
60°	11764
65°	11130
70°	10467
75°	9913
80°	9250
85°	8554



TEST NUMBER: P581827
 CATALOG NUMBER: HCC6S15D010MB-HM60525940-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.6	6.1
10°-20°	235.9	17.1
20°-30°	331.5	24.0
30°-40°	295.0	21.4
40°-50°	164.9	11.9
50°-60°	117.5	8.5
60°-70°	85.5	6.2
70°-80°	49.5	3.6
80°-90°	15.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.0	47.3
0°-40°	947.0	68.6
0°-60°	1229.3	89.1
0°-90°	1379.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1379.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	900	
5°	894	85
15°	840	236
25°	726	331
35°	482	295
45°	205	165
55°	130	117
65°	86	85
75°	47	49
85°	14	15
90°	0	



TEST NUMBER: P581827
CATALOG NUMBER: HCC6S15D010MB-HM60525940-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	899.5
2.5°	895.6
5°	893.7
7.5°	885.9
10°	870.3
12.5°	855.7
15°	840.1
17.5°	818.7
20°	790.4
22.5°	759.2
25°	726.1
27.5°	685.1
30°	633.4
32.5°	567.2
35°	482.4
37.5°	386.9
40°	304.1
42.5°	242.7
45°	204.6
47.5°	179.3
50°	160.8
52.5°	144.3
55°	129.6
57.5°	117.9
60°	107.3
62.5°	97.5
65°	85.8
67.5°	76.0
70°	65.3
72.5°	55.5
75°	46.8
77.5°	38.0
80°	29.3
82.5°	21.5
85°	13.6
87.5°	6.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)