

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593110

Luminaire Tested: **HCC6S15D010BZ-HM60525950-61WDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593110  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S15D010BZ-HM60525950-61WDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1441.0 lumens  
Efficiency: N/A  
Efficacy: 102.9 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593110  
CATALOG NUMBER: HCC6S15D010BZ-HM60525950-61WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P593110

CATALOG NUMBER: HCC6S15D010BZ-HM60525950-61WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59		
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50		
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	56432
5°	56813
10°	57469
15°	58650
20°	58974
25°	57142
30°	51837
35°	42148
40°	27974
45°	15568
50°	8733
55°	4846
60°	2675
65°	2011
70°	1394
75°	1038
80°	600
85°	629



TEST NUMBER: P593110  
 CATALOG NUMBER: HCC6S15D010BZ-HM60525950-61WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.5	6.8
10°-20°	291.4	20.2
20°-30°	429.5	29.8
30°-40°	384.1	26.7
40°-50°	166.7	11.6
50°-60°	49.0	3.4
60°-70°	15.6	1.1
70°-80°	5.5	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	819.4	56.9
0°-40°	1203.5	83.5
0°-60°	1419.1	98.5
0°-90°	1441.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1441.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1029	
5°	1032	99
15°	1033	291
25°	945	429
35°	630	384
45°	201	167
55°	51	49
65°	16	16
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P593110

CATALOG NUMBER: HCC6S15D010BZ-HM60525950-61WDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1029.4
2.5°	1026.6
5°	1032.4
7.5°	1034.3
10°	1032.4
12.5°	1032.4
15°	1033.4
17.5°	1027.5
20°	1010.9
22.5°	982.7
25°	944.7
27.5°	891.1
30°	818.9
32.5°	733.1
35°	629.8
37.5°	511.8
40°	390.9
42.5°	285.7
45°	200.8
47.5°	143.4
50°	102.4
52.5°	73.1
55°	50.7
57.5°	34.2
60°	24.4
62.5°	19.5
65°	15.5
67.5°	11.7
70°	8.7
72.5°	6.8
75°	4.9
77.5°	3.9
80°	1.9
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)