

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593115

Luminaire Tested: **HCC6W15D010BZ-HM60525950-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593115
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010BZ-HM60525950-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1345.6 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593115
CATALOG NUMBER: HCC6W15D010BZ-HM60525950-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P593115

CATALOG NUMBER: HCC6W15D010BZ-HM60525950-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50089
5°	49906
10°	49075
15°	48207
20°	46542
25°	44132
30°	40139
35°	32076
40°	21404
45°	15257
50°	12707
55°	11077
60°	10471
65°	9845
70°	9056
75°	8472
80°	7703
85°	6730



TEST NUMBER: P593115
 CATALOG NUMBER: HCC6W15D010BZ-HM60525950-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	6.4
10°-20°	238.5	17.7
20°-30°	333.3	24.8
30°-40°	293.6	21.8
40°-50°	158.6	11.8
50°-60°	106.0	7.9
60°-70°	75.2	5.6
70°-80°	42.3	3.1
80°-90°	12.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	657.6	48.9
0°-40°	951.2	70.7
0°-60°	1215.8	90.4
0°-90°	1345.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1345.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	914	
5°	907	86
15°	849	239
25°	730	333
35°	479	294
45°	197	159
55°	116	106
65°	76	75
75°	40	42
85°	11	12
90°	0	



TEST NUMBER: P593115
CATALOG NUMBER: HCC6W15D010BZ-HM60525950-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	913.7
2.5°	908.8
5°	906.9
7.5°	898.1
10°	881.6
12.5°	866.0
15°	849.4
17.5°	827.0
20°	797.8
22.5°	765.7
25°	729.6
27.5°	687.7
30°	634.1
32.5°	568.0
35°	479.3
37.5°	382.8
40°	299.1
42.5°	235.7
45°	196.8
47.5°	170.5
50°	149.0
52.5°	131.5
55°	115.9
57.5°	105.2
60°	95.5
62.5°	85.7
65°	75.9
67.5°	66.3
70°	56.5
72.5°	47.8
75°	40.0
77.5°	32.1
80°	24.4
82.5°	17.5
85°	10.7
87.5°	4.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)