

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581841

Luminaire Tested: **HCC6S20D010SL-HM60525827-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581841
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010SL-HM60525827-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1848.5 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581841
CATALOG NUMBER: HCC6S20D010SL-HM60525827-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581841

CATALOG NUMBER: HCC6S20D010SL-HM60525827-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89	89	89	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79	79	79	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70	70	70	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63	63	63	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57	57	57	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52	52	52	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48	48	48	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44	44	44	44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40	40	40	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37	37	37	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68816
5°	68556
10°	67417
15°	66226
20°	63939
25°	60633
30°	55148
35°	44062
40°	29398
45°	20956
50°	17458
55°	15225
60°	14374
65°	13529
70°	12438
75°	11607
80°	10544
85°	9246



TEST NUMBER: P581841
 CATALOG NUMBER: HCC6S20D010SL-HM60525827-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	6.4
10°-20°	327.7	17.7
20°-30°	457.9	24.8
30°-40°	403.3	21.8
40°-50°	217.9	11.8
50°-60°	145.7	7.9
60°-70°	103.2	5.6
70°-80°	58.0	3.1
80°-90°	16.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	903.4	48.9
0°-40°	1306.7	70.7
0°-60°	1670.3	90.4
0°-90°	1848.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1848.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1255	
5°	1246	118
15°	1167	328
25°	1002	458
35°	658	403
45°	270	218
55°	159	146
65°	104	103
75°	55	58
85°	15	17
90°	0	



TEST NUMBER: P581841

CATALOG NUMBER: HCC6S20D010SL-HM60525827-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1255.3
2.5°	1248.6
5°	1245.8
7.5°	1233.8
10°	1211.1
12.5°	1189.6
15°	1166.9
17.5°	1136.2
20°	1096.0
22.5°	1051.9
25°	1002.4
27.5°	944.8
30°	871.2
32.5°	780.2
35°	658.4
37.5°	525.9
40°	410.8
42.5°	323.8
45°	270.3
47.5°	234.2
50°	204.7
52.5°	180.7
55°	159.3
57.5°	144.6
60°	131.1
62.5°	117.7
65°	104.3
67.5°	91.0
70°	77.6
72.5°	65.6
75°	54.8
77.5°	44.2
80°	33.4
82.5°	24.1
85°	14.7
87.5°	6.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)