

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581851

Luminaire Tested: **HCC6W20D010SL-HM60525827-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581851
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W20D010SL-HM60525827-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1954.2 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581851
CATALOG NUMBER: HCC6W20D010SL-HM60525827-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P581851

CATALOG NUMBER: HCC6W20D010SL-HM60525827-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66689
5°	66652
10°	66003
15°	65318
20°	63472
25°	60796
30°	56420
35°	48539
40°	35431
45°	24282
50°	19522
55°	17013
60°	15700
65°	14930
70°	13945
75°	13026
80°	11839
85°	10127



TEST NUMBER: P581851
 CATALOG NUMBER: HCC6W20D010SL-HM60525827-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	5.9
10°-20°	323.2	16.5
20°-30°	459.7	23.5
30°-40°	442.6	22.6
40°-50°	254.7	13.0
50°-60°	161.4	8.3
60°-70°	114.2	5.8
70°-80°	65.1	3.3
80°-90°	18.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	897.8	45.9
0°-40°	1340.3	68.6
0°-60°	1756.4	89.9
0°-90°	1954.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1954.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1216	
5°	1211	115
15°	1151	323
25°	1005	460
35°	725	443
45°	313	255
55°	178	161
65°	115	114
75°	62	65
85°	16	19
90°	0	



TEST NUMBER: P581851
CATALOG NUMBER: HCC6W20D010SL-HM60525827-61WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1216.5
2.5°	1211.2
5°	1211.2
7.5°	1203.1
10°	1185.7
12.5°	1168.3
15°	1150.9
17.5°	1124.2
20°	1088.0
22.5°	1047.9
25°	1005.1
27.5°	952.9
30°	891.3
32.5°	816.3
35°	725.3
37.5°	614.3
40°	495.1
42.5°	390.8
45°	313.2
47.5°	263.6
50°	228.9
52.5°	200.8
55°	178.0
57.5°	157.9
60°	143.2
62.5°	129.8
65°	115.1
67.5°	101.7
70°	87.0
72.5°	73.6
75°	61.5
77.5°	49.5
80°	37.5
82.5°	26.7
85°	16.1
87.5°	6.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)