

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581876

Luminaire Tested: **HCC6S20D010SL-HM60525835-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010SL-HM60525835-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2072.7 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581876
CATALOG NUMBER: HCC6S20D010SL-HM60525835-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P581876
 CATALOG NUMBER: HCC6S20D010SL-HM60525835-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86	83	80	79
4	96	88	82	77	94	86	81	77	84	79	76		82	78	75		80	77	74	72
5	90	81	75	71	89	80	75	70	79	74	70		77	73	69		75	72	68	67
6	85	76	70	65	84	75	69	65	74	68	64		72	67	64		71	67	63	62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67	62	59	57
8	77	67	60	56	75	66	60	56	65	59	55		64	59	55		63	58	55	53
9	73	62	56	52	72	62	56	52	61	56	52		60	55	52		59	55	51	50
10	69	59	53	49	68	58	52	48	57	52	48		57	52	48		56	51	48	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103807
5°	103714
10°	102637
15°	100574
20°	95272
25°	86037
30°	73081
35°	53967
40°	31208
45°	16568
50°	9364
55°	4893
60°	3201
65°	2283
70°	1635
75°	1250
80°	916
85°	943



TEST NUMBER: P581876
 CATALOG NUMBER: HCC6S20D010SL-HM60525835-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.6	8.6
10°-20°	495.6	23.9
20°-30°	646.9	31.2
30°-40°	494.4	23.9
40°-50°	179.0	8.6
50°-60°	52.0	2.5
60°-70°	18.6	0.9
70°-80°	6.4	0.3
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1321.2	63.7
0°-40°	1815.6	87.6
0°-60°	2046.5	98.7
0°-90°	2072.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2072.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1894	
5°	1885	179
15°	1772	496
25°	1422	647
35°	806	494
45°	214	179
55°	51	52
65°	18	19
75°	6	6
85°	2	1
90°	0	



TEST NUMBER: P581876
CATALOG NUMBER: HCC6S20D010SL-HM60525835-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1893.6
2.5°	1884.7
5°	1884.7
7.5°	1871.6
10°	1843.8
12.5°	1811.7
15°	1772.1
17.5°	1713.5
20°	1633.1
22.5°	1533.6
25°	1422.4
27.5°	1296.5
30°	1154.5
32.5°	995.1
35°	806.4
37.5°	608.8
40°	436.1
42.5°	301.5
45°	213.7
47.5°	153.6
50°	109.8
52.5°	77.6
55°	51.2
57.5°	36.6
60°	29.2
62.5°	23.5
65°	17.6
67.5°	14.6
70°	10.2
72.5°	7.4
75°	5.9
77.5°	4.4
80°	2.9
82.5°	1.5
85°	1.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)