

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581888

Luminaire Tested: **HCC6S20D010SL-HM60525835-61WDWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010SL-HM60525835-61WDWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2300.8 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581888
CATALOG NUMBER: HCC6S20D010SL-HM60525835-61WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P581888
 CATALOG NUMBER: HCC6S20D010SL-HM60525835-61WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69		
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85815
5°	86545
10°	89661
15°	97390
20°	101305
25°	96895
30°	83627
35°	60211
40°	33921
45°	17575
50°	10482
55°	7551
60°	6414
65°	7407
70°	9377
75°	9913
80°	9692
85°	9183



TEST NUMBER: P581888
 CATALOG NUMBER: HCC6S20D010SL-HM60525835-61WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	6.6
10°-20°	484.0	21.0
20°-30°	723.4	31.4
30°-40°	553.0	24.0
40°-50°	193.1	8.4
50°-60°	73.6	3.2
60°-70°	57.7	2.5
70°-80°	48.8	2.1
80°-90°	15.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1358.8	59.1
0°-40°	1911.8	83.1
0°-60°	2178.5	94.7
0°-90°	2300.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2300.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1565	
5°	1573	151
15°	1716	484
25°	1602	723
35°	900	553
45°	227	193
55°	79	74
65°	57	58
75°	47	49
85°	15	16
90°	0	



TEST NUMBER: P581888
CATALOG NUMBER: HCC6S20D010SL-HM60525835-61WDWB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1565.4
2.5°	1560.9
5°	1572.7
7.5°	1588.8
10°	1610.7
12.5°	1660.4
15°	1716.0
17.5°	1749.7
20°	1736.5
22.5°	1683.9
25°	1601.9
27.5°	1484.9
30°	1321.1
32.5°	1125.1
35°	899.7
37.5°	667.1
40°	474.0
42.5°	332.1
45°	226.7
47.5°	159.4
50°	122.9
52.5°	96.5
55°	79.0
57.5°	64.4
60°	58.5
62.5°	57.1
65°	57.1
67.5°	59.9
70°	58.5
72.5°	54.2
75°	46.8
77.5°	39.5
80°	30.7
82.5°	22.0
85°	14.6
87.5°	5.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)