

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593128

Luminaire Tested: **HCC6S20D010BZ-HM60525850-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010BZ-HM60525850-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2233.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593128
CATALOG NUMBER: HCC6S20D010BZ-HM60525850-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P593128
 CATALOG NUMBER: HCC6S20D010BZ-HM60525850-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59		
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50		
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87455
5°	88036
10°	89054
15°	90880
20°	91393
25°	88541
30°	80329
35°	65310
40°	43353
45°	24127
50°	13526
55°	7503
60°	4133
65°	3126
70°	2180
75°	1610
80°	979
85°	943



TEST NUMBER: P593128
 CATALOG NUMBER: HCC6S20D010BZ-HM60525850-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.7	6.8
10°-20°	451.5	20.2
20°-30°	665.5	29.8
30°-40°	595.2	26.7
40°-50°	258.3	11.6
50°-60°	75.9	3.4
60°-70°	24.2	1.1
70°-80°	8.5	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1269.7	56.9
0°-40°	1864.9	83.5
0°-60°	2199.0	98.5
0°-90°	2233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2233.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1595	
5°	1600	153
15°	1601	452
25°	1464	665
35°	976	595
45°	311	258
55°	78	76
65°	24	24
75°	8	9
85°	2	1
90°	0	



TEST NUMBER: P593128
CATALOG NUMBER: HCC6S20D010BZ-HM60525850-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1595.3
2.5°	1590.7
5°	1599.8
7.5°	1602.9
10°	1599.8
12.5°	1599.8
15°	1601.3
17.5°	1592.2
20°	1566.6
22.5°	1522.8
25°	1463.8
27.5°	1380.8
30°	1269.0
32.5°	1136.1
35°	975.9
37.5°	793.1
40°	605.8
42.5°	442.7
45°	311.2
47.5°	222.1
50°	158.6
52.5°	113.3
55°	78.5
57.5°	52.9
60°	37.7
62.5°	30.3
65°	24.1
67.5°	18.1
70°	13.6
72.5°	10.5
75°	7.6
77.5°	6.0
80°	3.1
82.5°	1.5
85°	1.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)