

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593133

Luminaire Tested: **HCC6S20D010MB-HM60525850-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593133
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010MB-HM60525850-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2085.1 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593133
CATALOG NUMBER: HCC6S20D010MB-HM60525850-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P593133
 CATALOG NUMBER: HCC6S20D010MB-HM60525850-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79				
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70				
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63				
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57				
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52				
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48				
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44				
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40				
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77620
5°	77333
10°	76045
15°	74700
20°	72118
25°	68387
30°	62206
35°	49704
40°	33162
45°	23638
50°	19692
55°	17165
60°	16227
65°	15268
70°	14041
75°	13111
80°	11902
85°	10504



TEST NUMBER: P593133
 CATALOG NUMBER: HCC6S20D010MB-HM60525850-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.9	6.4
10°-20°	369.6	17.7
20°-30°	516.5	24.8
30°-40°	454.9	21.8
40°-50°	245.8	11.8
50°-60°	164.3	7.9
60°-70°	116.5	5.6
70°-80°	65.5	3.1
80°-90°	19.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1018.9	48.9
0°-40°	1473.9	70.7
0°-60°	1884.0	90.4
0°-90°	2085.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2085.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1416	
5°	1405	133
15°	1316	370
25°	1131	516
35°	743	455
45°	305	246
55°	180	164
65°	118	116
75°	62	66
85°	17	19
90°	0	



TEST NUMBER: P593133

CATALOG NUMBER: HCC6S20D010MB-HM60525850-61MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1415.9
2.5°	1408.3
5°	1405.3
7.5°	1391.7
10°	1366.1
12.5°	1341.9
15°	1316.2
17.5°	1281.5
20°	1236.2
22.5°	1186.5
25°	1130.6
27.5°	1065.7
30°	982.7
32.5°	880.0
35°	742.7
37.5°	593.2
40°	463.4
42.5°	365.3
45°	304.9
47.5°	264.1
50°	230.9
52.5°	203.8
55°	179.6
57.5°	163.0
60°	148.0
62.5°	132.8
65°	117.7
67.5°	102.6
70°	87.6
72.5°	74.0
75°	61.9
77.5°	49.9
80°	37.7
82.5°	27.2
85°	16.7
87.5°	7.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)