

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581941

Luminaire Tested: **HCC6W20D010BZ-HM60525930-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W20D010BZ-HM60525930-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1801.7 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581941
CATALOG NUMBER: HCC6W20D010BZ-HM60525930-61WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581941

CATALOG NUMBER: HCC6W20D010BZ-HM60525930-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89	
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78	
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69	
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62	
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56	
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51	
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46	
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42	
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39	
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61486
5°	61446
10°	60848
15°	60222
20°	58525
25°	56048
30°	52021
35°	44751
40°	32668
45°	22382
50°	17995
55°	15684
60°	14473
65°	13776
70°	12855
75°	12031
80°	10923
85°	9309



TEST NUMBER: P581941
 CATALOG NUMBER: HCC6W20D010BZ-HM60525930-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	5.9
10°-20°	298.0	16.5
20°-30°	423.8	23.5
30°-40°	408.0	22.6
40°-50°	234.8	13.0
50°-60°	148.7	8.3
60°-70°	105.3	5.8
70°-80°	60.1	3.3
80°-90°	17.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	827.7	45.9
0°-40°	1235.7	68.6
0°-60°	1619.3	89.9
0°-90°	1801.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1801.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1122	
5°	1117	106
15°	1061	298
25°	927	424
35°	669	408
45°	289	235
55°	164	149
65°	106	105
75°	57	60
85°	15	17
90°	0	



TEST NUMBER: P581941

CATALOG NUMBER: HCC6W20D010BZ-HM60525930-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1121.6
2.5°	1116.6
5°	1116.6
7.5°	1109.2
10°	1093.1
12.5°	1077.1
15°	1061.1
17.5°	1036.5
20°	1003.2
22.5°	966.1
25°	926.6
27.5°	878.5
30°	821.8
32.5°	752.7
35°	668.7
37.5°	566.3
40°	456.5
42.5°	360.3
45°	288.7
47.5°	243.0
50°	211.0
52.5°	185.0
55°	164.1
57.5°	145.6
60°	132.0
62.5°	119.6
65°	106.2
67.5°	93.8
70°	80.2
72.5°	67.9
75°	56.8
77.5°	45.7
80°	34.6
82.5°	24.7
85°	14.8
87.5°	6.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)