

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581950

Luminaire Tested: **HCC6W20D010MW-HM60525935-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W20D010MW-HM60525935-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1886.2 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581950
CATALOG NUMBER: HCC6W20D010MW-HM60525935-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P581950
 CATALOG NUMBER: HCC6W20D010MW-HM60525935-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	66	62	61
8	79	70	64	59	78	69	63	59	68	63	59	67	62	59	66	62	59	57
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115473
5°	114984
10°	112261
15°	106567
20°	94987
25°	80013
30°	63744
35°	45481
40°	24453
45°	10482
50°	4767
55°	1739
60°	855
65°	675
70°	625
75°	254
80°	379
85°	0



TEST NUMBER: P581950
 CATALOG NUMBER: HCC6W20D010MW-HM60525935-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.2	10.5
10°-20°	520.5	27.6
20°-30°	602.8	32.0
30°-40°	416.8	22.1
40°-50°	120.4	6.4
50°-60°	20.7	1.1
60°-70°	5.3	0.3
70°-80°	2.0	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1320.5	70.0
0°-40°	1737.4	92.1
0°-60°	1878.5	99.6
0°-90°	1886.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1886.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2106	
5°	2090	197
15°	1878	520
25°	1323	603
35°	680	417
45°	135	120
55°	18	21
65°	5	5
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P581950
CATALOG NUMBER: HCC6W20D010MW-HM60525935-61NDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2106.4
2.5°	2097.3
5°	2089.5
7.5°	2066.1
10°	2016.7
12.5°	1956.9
15°	1877.7
17.5°	1765.9
20°	1628.2
22.5°	1476.2
25°	1322.8
27.5°	1165.6
30°	1007.0
32.5°	848.5
35°	679.6
37.5°	504.2
40°	341.7
42.5°	215.7
45°	135.2
47.5°	87.0
50°	55.9
52.5°	33.8
55°	18.2
57.5°	10.4
60°	7.8
62.5°	6.5
65°	5.2
67.5°	3.9
70°	3.9
72.5°	2.6
75°	1.2
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)