

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581951

Luminaire Tested: **HCC6W20D010MW-HM60525935-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W20D010MW-HM60525935-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1768.1 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581951
CATALOG NUMBER: HCC6W20D010MW-HM60525935-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P581951

CATALOG NUMBER: HCC6W20D010MW-HM60525935-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66968
5°	66652
10°	65185
15°	63655
20°	61261
25°	57935
30°	52647
35°	42610
40°	28732
45°	19746
50°	16187
55°	14164
60°	13387
65°	12634
70°	11877
75°	11289
80°	10260
85°	8995



TEST NUMBER: P581951
 CATALOG NUMBER: HCC6W20D010MW-HM60525935-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.3	6.5
10°-20°	315.0	17.8
20°-30°	437.6	24.7
30°-40°	389.6	22.0
40°-50°	206.8	11.7
50°-60°	135.3	7.7
60°-70°	96.9	5.5
70°-80°	56.2	3.2
80°-90°	16.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	866.9	49.0
0°-40°	1256.4	71.1
0°-60°	1598.5	90.4
0°-90°	1768.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1768.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1222	
5°	1211	114
15°	1122	315
25°	958	438
35°	637	390
45°	255	207
55°	148	135
65°	97	97
75°	53	56
85°	14	16
90°	0	



TEST NUMBER: P581951
CATALOG NUMBER: HCC6W20D010MW-HM60525935-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1221.6
2.5°	1215.1
5°	1211.2
7.5°	1196.9
10°	1171.0
12.5°	1147.5
15°	1121.6
17.5°	1089.0
20°	1050.1
22.5°	1005.9
25°	957.8
27.5°	901.9
30°	831.7
32.5°	747.2
35°	636.7
37.5°	514.6
40°	401.5
42.5°	311.9
45°	254.7
47.5°	217.1
50°	189.8
52.5°	167.7
55°	148.2
57.5°	133.8
60°	122.1
62.5°	110.5
65°	97.4
67.5°	85.8
70°	74.1
72.5°	63.7
75°	53.3
77.5°	42.9
80°	32.5
82.5°	23.3
85°	14.3
87.5°	6.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)