

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581984

Luminaire Tested: **HCC6W25D010SL-HM60525827-61MDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581984  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W25D010SL-HM60525827-61MDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2352.0 lumens  
Efficiency: N/A  
Efficacy: 87.8 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581984  
CATALOG NUMBER: HCC6W25D010SL-HM60525827-61MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581984  
 CATALOG NUMBER: HCC6W25D010SL-HM60525827-61MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79		
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72		
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67		
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62		
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57		
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53		
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50		
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117798
5°	117692
10°	116470
15°	114127
20°	108113
25°	97633
30°	82930
35°	61228
40°	35409
45°	18800
50°	10618
55°	5553
60°	3640
65°	2581
70°	1875
75°	1398
80°	1073
85°	1006



TEST NUMBER: P581984  
 CATALOG NUMBER: HCC6W25D010SL-HM60525827-61MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.7	8.6
10°-20°	562.4	23.9
20°-30°	734.1	31.2
30°-40°	561.0	23.9
40°-50°	203.1	8.6
50°-60°	59.0	2.5
60°-70°	21.1	0.9
70°-80°	7.2	0.3
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1499.2	63.7
0°-40°	2060.2	87.6
0°-60°	2322.3	98.7
0°-90°	2352.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2352.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2149	
5°	2139	203
15°	2011	562
25°	1614	734
35°	915	561
45°	242	203
55°	58	59
65°	20	21
75°	7	7
85°	2	1
90°	0	



TEST NUMBER: P581984  
CATALOG NUMBER: HCC6W25D010SL-HM60525827-61MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2148.8
2.5°	2138.7
5°	2138.7
7.5°	2123.8
10°	2092.3
12.5°	2055.8
15°	2010.9
17.5°	1944.5
20°	1853.2
22.5°	1740.3
25°	1614.1
27.5°	1471.3
30°	1310.1
32.5°	1129.2
35°	914.9
37.5°	690.8
40°	494.8
42.5°	342.1
45°	242.5
47.5°	174.4
50°	124.5
52.5°	88.0
55°	58.1
57.5°	41.5
60°	33.2
62.5°	26.6
65°	19.9
67.5°	16.7
70°	11.7
72.5°	8.3
75°	6.6
77.5°	5.0
80°	3.4
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)