

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582006

Luminaire Tested: **HCC6W25D010SL-HM60525830-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582006  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W25D010SL-HM60525830-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2429.5 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582006  
CATALOG NUMBER: HCC6W25D010SL-HM60525830-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582006  
 CATALOG NUMBER: HCC6W25D010SL-HM60525830-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84		89	85	83		86	83	81	79
3	97	88	82	77	94	87	81	76	84	79	75		81	77	73		79	75	72	70
4	90	81	73	68	88	79	73	68	77	71	67		75	70	66		73	69	65	63
5	84	74	67	61	83	73	66	61	71	65	60		69	64	60		67	63	59	57
6	79	68	61	55	77	67	60	55	66	59	55		64	59	54		63	58	54	52
7	74	63	56	50	73	62	55	50	61	55	50		60	54	50		58	53	49	48
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54	49	46	44
9	66	55	48	43	65	54	47	43	53	47	42		52	46	42		51	46	42	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92021
5°	91591
10°	89566
15°	87464
20°	84182
25°	79613
30°	72347
35°	58558
40°	39488
45°	27135
50°	22234
55°	19459
60°	18409
65°	17369
70°	16301
75°	15504
80°	14080
85°	12391



TEST NUMBER: P582006  
 CATALOG NUMBER: HCC6W25D010SL-HM60525830-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.1	6.5
10°-20°	432.8	17.8
20°-30°	601.3	24.7
30°-40°	535.4	22.0
40°-50°	284.2	11.7
50°-60°	185.9	7.6
60°-70°	133.2	5.5
70°-80°	77.2	3.2
80°-90°	22.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1191.2	49.0
0°-40°	1726.5	71.1
0°-60°	2196.6	90.4
0°-90°	2429.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2429.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1679	
5°	1664	157
15°	1541	433
25°	1316	601
35°	875	535
45°	350	284
55°	204	186
65°	134	133
75°	73	77
85°	20	23
90°	0	



TEST NUMBER: P582006

CATALOG NUMBER: HCC6W25D010SL-HM60525830-61NDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1678.6
2.5°	1669.7
5°	1664.4
7.5°	1644.7
10°	1609.0
12.5°	1576.8
15°	1541.1
17.5°	1496.5
20°	1443.0
22.5°	1382.2
25°	1316.2
27.5°	1239.3
30°	1142.9
32.5°	1026.8
35°	875.0
37.5°	707.2
40°	551.8
42.5°	428.5
45°	350.0
47.5°	298.2
50°	260.7
52.5°	230.4
55°	203.6
57.5°	183.9
60°	167.9
62.5°	151.7
65°	133.9
67.5°	117.9
70°	101.7
72.5°	87.5
75°	73.2
77.5°	58.9
80°	44.6
82.5°	32.2
85°	19.7
87.5°	8.9
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)