

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582024

Luminaire Tested: **HCC6W25D010BZ-HM60525835-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582024  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W25D010BZ-HM60525835-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2468.6 lumens  
Efficiency: N/A  
Efficacy: 92.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582024  
CATALOG NUMBER: HCC6W25D010BZ-HM60525835-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582024  
 CATALOG NUMBER: HCC6W25D010BZ-HM60525835-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93501
5°	93055
10°	91003
15°	88871
20°	85530
25°	80884
30°	73511
35°	59501
40°	40125
45°	27569
50°	22592
55°	19775
60°	18694
65°	17654
70°	16573
75°	15759
80°	14333
85°	12517



TEST NUMBER: P582024  
 CATALOG NUMBER: HCC6W25D010BZ-HM60525835-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.6	6.5
10°-20°	439.7	17.8
20°-30°	610.9	24.7
30°-40°	544.0	22.0
40°-50°	288.7	11.7
50°-60°	188.8	7.6
60°-70°	135.3	5.5
70°-80°	78.5	3.2
80°-90°	22.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1210.3	49.0
0°-40°	1754.3	71.1
0°-60°	2231.9	90.4
0°-90°	2468.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2468.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1706	
5°	1691	160
15°	1566	440
25°	1337	611
35°	889	544
45°	356	289
55°	207	189
65°	136	135
75°	74	79
85°	20	23
90°	0	



TEST NUMBER: P582024

CATALOG NUMBER: HCC6W25D010BZ-HM60525835-61NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1705.6
2.5°	1696.6
5°	1691.0
7.5°	1671.1
10°	1634.8
12.5°	1602.2
15°	1565.9
17.5°	1520.5
20°	1466.1
22.5°	1404.4
25°	1337.2
27.5°	1259.3
30°	1161.3
32.5°	1043.4
35°	889.1
37.5°	718.5
40°	560.7
42.5°	435.4
45°	355.6
47.5°	303.0
50°	264.9
52.5°	234.1
55°	206.9
57.5°	186.9
60°	170.5
62.5°	154.2
65°	136.1
67.5°	119.8
70°	103.4
72.5°	89.0
75°	74.4
77.5°	59.9
80°	45.4
82.5°	32.7
85°	19.9
87.5°	9.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)