

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582040

Luminaire Tested: **HCC6W25D010BZ-HM60525840-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W25D010BZ-HM60525840-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2956.5 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582040
CATALOG NUMBER: HCC6W25D010BZ-HM60525840-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582040
 CATALOG NUMBER: HCC6W25D010BZ-HM60525840-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96		94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89		87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83		82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78		76
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73		71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68		67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64		62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60		59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56		55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176565
5°	176926
10°	179834
15°	181147
20°	165588
25°	130120
30°	95243
35°	67559
40°	31960
45°	12195
50°	5458
55°	1481
60°	636
65°	506
70°	305
75°	402
80°	0
85°	0



TEST NUMBER: P582040
 CATALOG NUMBER: HCC6W25D010BZ-HM60525840-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.6	10.4
10°-20°	882.2	29.8
20°-30°	981.3	33.2
30°-40°	613.0	20.7
40°-50°	145.7	4.9
50°-60°	20.8	0.7
60°-70°	4.3	0.1
70°-80°	1.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2171.0	73.4
0°-40°	2784.0	94.2
0°-60°	2950.5	99.8
0°-90°	2956.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2956.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3221	
5°	3215	308
15°	3192	882
25°	2151	981
35°	1010	613
45°	157	146
55°	16	21
65°	4	4
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582040
CATALOG NUMBER: HCC6W25D010BZ-HM60525840-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3220.8
2.5°	3207.3
5°	3215.1
7.5°	3226.7
10°	3230.6
12.5°	3228.6
15°	3191.8
17.5°	3067.5
20°	2838.4
22.5°	2516.1
25°	2151.2
27.5°	1801.7
30°	1504.6
32.5°	1258.0
35°	1009.5
37.5°	741.7
40°	446.6
42.5°	258.2
45°	157.3
47.5°	101.0
50°	64.0
52.5°	36.8
55°	15.5
57.5°	7.8
60°	5.8
62.5°	5.8
65°	3.9
67.5°	3.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	1.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)