

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593168

Luminaire Tested: **HCC6S25D010MW-HM60525850-61WDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593168  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S25D010MW-HM60525850-61WDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3131.2 lumens  
Efficiency: N/A  
Efficacy: 116.8 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593168  
CATALOG NUMBER: HCC6S25D010MW-HM60525850-61WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P593168  
 CATALOG NUMBER: HCC6S25D010MW-HM60525850-61WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52
9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	111011
5°	112502
10°	116720
15°	126936
20°	141920
25°	149386
30°	131508
35°	91209
40°	54466
45°	25886
50°	9765
55°	4081
60°	1283
65°	1012
70°	625
75°	402
80°	600
85°	0



TEST NUMBER: P593168  
 CATALOG NUMBER: HCC6S25D010MW-HM60525850-61WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	196.8	6.3
10°-20°	642.2	20.5
20°-30°	1100.5	35.1
30°-40°	854.7	27.3
40°-50°	282.5	9.0
50°-60°	43.3	1.4
60°-70°	7.6	0.2
70°-80°	2.8	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1939.5	61.9
0°-40°	2794.2	89.2
0°-60°	3120.0	99.6
0°-90°	3131.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3131.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2025	
5°	2044	197
15°	2237	642
25°	2470	1100
35°	1363	855
45°	334	283
55°	43	43
65°	8	8
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P593168  
CATALOG NUMBER: HCC6S25D010MW-HM60525850-61WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2025.0
2.5°	2023.1
5°	2044.4
7.5°	2067.7
10°	2096.8
12.5°	2155.0
15°	2236.6
17.5°	2335.6
20°	2432.7
22.5°	2489.0
25°	2469.7
27.5°	2335.6
30°	2077.5
32.5°	1729.9
35°	1362.9
37.5°	1034.9
40°	761.1
42.5°	537.8
45°	333.9
47.5°	186.4
50°	114.5
52.5°	69.9
55°	42.7
57.5°	21.3
60°	11.7
62.5°	9.6
65°	7.8
67.5°	5.8
70°	3.9
72.5°	3.9
75°	1.9
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)