

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582091

Luminaire Tested: **HCC6S25D010BZ-HM60525935-61MDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582091  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S25D010BZ-HM60525935-61MDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2540.5 lumens  
Efficiency: N/A  
Efficacy: 94.8 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582091  
CATALOG NUMBER: HCC6S25D010BZ-HM60525935-61MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582091

CATALOG NUMBER: HCC6S25D010BZ-HM60525935-61MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120637
5°	122523
10°	129495
15°	144189
20°	149527
25°	122693
30°	85969
35°	58658
40°	30550
45°	10745
50°	4810
55°	1548
60°	877
65°	636
70°	529
75°	339
80°	0
85°	0



TEST NUMBER: P582091  
 CATALOG NUMBER: HCC6S25D010BZ-HM60525935-61MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	215.7	8.5
10°-20°	714.5	28.1
20°-30°	909.8	35.8
30°-40°	542.2	21.3
40°-50°	131.5	5.2
50°-60°	20.2	0.8
60°-70°	5.0	0.2
70°-80°	1.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1840.0	72.4
0°-40°	2382.2	93.8
0°-60°	2533.9	99.7
0°-90°	2540.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2540.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2201	
5°	2226	216
15°	2541	715
25°	2028	910
35°	876	542
45°	139	131
55°	16	20
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582091  
CATALOG NUMBER: HCC6S25D010BZ-HM60525935-61MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2200.6
2.5°	2200.6
5°	2226.5
7.5°	2266.8
10°	2326.3
12.5°	2419.8
15°	2540.6
17.5°	2616.4
20°	2563.1
22.5°	2358.6
25°	2028.4
27.5°	1664.2
30°	1358.1
32.5°	1110.0
35°	876.5
37.5°	646.0
40°	426.9
42.5°	230.4
45°	138.6
47.5°	87.0
50°	56.4
52.5°	33.8
55°	16.2
57.5°	9.6
60°	8.0
62.5°	6.4
65°	4.9
67.5°	3.3
70°	3.3
72.5°	1.6
75°	1.6
77.5°	1.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)