

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582101

Luminaire Tested: **HCC6S25D010SL-HM60525935-61WDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582101  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S25D010SL-HM60525935-61WDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2598.6 lumens  
Efficiency: N/A  
Efficacy: 97.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582101  
CATALOG NUMBER: HCC6S25D010SL-HM60525935-61WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582101  
 CATALOG NUMBER: HCC6S25D010SL-HM60525935-61WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52
9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92120
5°	93363
10°	96859
15°	105341
20°	117774
25°	123963
30°	109131
35°	75697
40°	45199
45°	21491
50°	8111
55°	3393
60°	1053
65°	830
70°	529
75°	339
80°	505
85°	0



TEST NUMBER: P582101  
 CATALOG NUMBER: HCC6S25D010SL-HM60525935-61WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.3	6.3
10°-20°	533.0	20.5
20°-30°	913.3	35.1
30°-40°	709.3	27.3
40°-50°	234.5	9.0
50°-60°	36.0	1.4
60°-70°	6.4	0.2
70°-80°	2.4	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1609.5	61.9
0°-40°	2318.8	89.2
0°-60°	2589.2	99.6
0°-90°	2598.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2598.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1680	
5°	1697	163
15°	1856	533
25°	2049	913
35°	1131	709
45°	277	234
55°	36	36
65°	6	6
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P582101  
CATALOG NUMBER: HCC6S25D010SL-HM60525935-61WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1680.4
2.5°	1678.9
5°	1696.6
7.5°	1715.9
10°	1740.0
12.5°	1788.4
15°	1856.1
17.5°	1938.3
20°	2018.8
22.5°	2065.6
25°	2049.4
27.5°	1938.3
30°	1724.0
32.5°	1435.6
35°	1131.1
37.5°	858.8
40°	631.6
42.5°	446.3
45°	277.2
47.5°	154.6
50°	95.1
52.5°	58.0
55°	35.5
57.5°	17.7
60°	9.6
62.5°	8.0
65°	6.4
67.5°	4.9
70°	3.3
72.5°	3.3
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)