

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582097

Luminaire Tested: **HCC6S25D010MW-HM60525935-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S25D010MW-HM60525935-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2281.2 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582097
CATALOG NUMBER: HCC6S25D010MW-HM60525935-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582097

CATALOG NUMBER: HCC6S25D010MW-HM60525935-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81534
5°	81317
10°	80098
15°	78831
20°	76242
25°	72615
30°	66301
35°	53385
40°	35975
45°	26235
50°	22677
55°	20482
60°	19439
65°	18394
70°	17311
75°	16373
80°	15280
85°	14215



TEST NUMBER: P582097
 CATALOG NUMBER: HCC6S25D010MW-HM60525935-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.9	6.1
10°-20°	390.1	17.1
20°-30°	548.0	24.0
30°-40°	487.8	21.4
40°-50°	272.6	12.0
50°-60°	194.2	8.5
60°-70°	141.3	6.2
70°-80°	81.8	3.6
80°-90°	25.5	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1077.9	47.3
0°-40°	1565.8	68.6
0°-60°	2032.6	89.1
0°-90°	2281.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2281.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1487	
5°	1478	140
15°	1389	390
25°	1200	548
35°	798	488
45°	338	273
55°	214	194
65°	142	141
75°	77	82
85°	23	25
90°	0	



TEST NUMBER: P582097
CATALOG NUMBER: HCC6S25D010MW-HM60525935-61PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1487.3
2.5°	1480.8
5°	1477.7
7.5°	1464.8
10°	1438.9
12.5°	1414.8
15°	1389.0
17.5°	1353.5
20°	1306.9
22.5°	1255.3
25°	1200.5
27.5°	1132.8
30°	1047.4
32.5°	937.9
35°	797.7
37.5°	639.7
40°	502.7
42.5°	401.2
45°	338.4
47.5°	296.5
50°	265.9
52.5°	238.4
55°	214.3
57.5°	195.0
60°	177.3
62.5°	161.1
65°	141.8
67.5°	125.7
70°	108.0
72.5°	91.8
75°	77.3
77.5°	62.9
80°	48.4
82.5°	35.5
85°	22.6
87.5°	11.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)