

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582093

Luminaire Tested: **HCC6W25D010SL-HM60525935-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W25D010SL-HM60525935-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2224.7 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582093
CATALOG NUMBER: HCC6W25D010SL-HM60525935-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P582093

CATALOG NUMBER: HCC6W25D010SL-HM60525935-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82817
5°	82517
10°	81139
15°	79711
20°	76948
25°	72972
30°	66371
35°	53030
40°	35381
45°	25220
50°	21023
55°	18322
60°	17312
65°	16305
70°	14987
75°	13979
80°	12691
85°	11133



TEST NUMBER: P582093
 CATALOG NUMBER: HCC6W25D010SL-HM60525935-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.8	6.4
10°-20°	394.3	17.7
20°-30°	551.1	24.8
30°-40°	485.4	21.8
40°-50°	262.2	11.8
50°-60°	175.4	7.9
60°-70°	124.3	5.6
70°-80°	69.8	3.1
80°-90°	20.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1087.2	48.9
0°-40°	1572.6	70.7
0°-60°	2010.2	90.4
0°-90°	2224.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2224.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1511	
5°	1500	142
15°	1404	394
25°	1206	551
35°	792	485
45°	325	262
55°	192	175
65°	126	124
75°	66	70
85°	18	20
90°	0	



TEST NUMBER: P582093
CATALOG NUMBER: HCC6W25D010SL-HM60525935-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1510.7
2.5°	1502.7
5°	1499.5
7.5°	1484.9
10°	1457.6
12.5°	1431.8
15°	1404.5
17.5°	1367.4
20°	1319.0
22.5°	1265.9
25°	1206.4
27.5°	1137.1
30°	1048.5
32.5°	939.0
35°	792.4
37.5°	633.0
40°	494.4
42.5°	389.8
45°	325.3
47.5°	281.8
50°	246.5
52.5°	217.4
55°	191.7
57.5°	173.9
60°	157.9
62.5°	141.7
65°	125.7
67.5°	109.5
70°	93.5
72.5°	78.9
75°	66.0
77.5°	53.1
80°	40.2
82.5°	28.9
85°	17.7
87.5°	8.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)