

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593178

Luminaire Tested: **HCC6W25D010MB-HM60525950-61WDBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593178  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W25D010MB-HM60525950-61WDBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2153.1 lumens  
Efficiency: N/A  
Efficacy: 80.3 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593178  
CATALOG NUMBER: HCC6W25D010MB-HM60525950-61WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P593178  
 CATALOG NUMBER: HCC6W25D010MB-HM60525950-61WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94	92
2	107	101	97	93	104	100	95	92	96	93	90		93	91	88		90	88	86	85
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74		81	77	73		79	75	72	71
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		73	69	66	65
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	68	62	57	77	68	61	57	66	61	57		65	60	56		64	59	56	54
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60	55	52	50
9	70	59	53	48	69	59	53	48	58	52	48		57	52	48		56	51	48	46
10	66	56	49	45	65	55	49	45	54	48	45		53	48	44		53	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	76463
5°	77025
10°	78372
15°	81482
20°	84894
25°	87924
30°	86748
35°	72277
40°	46351
45°	23150
50°	9177
55°	3116
60°	888
65°	636
70°	529
75°	699
80°	505
85°	0



TEST NUMBER: P593178  
 CATALOG NUMBER: HCC6W25D010MB-HM60525950-61WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.8	6.2
10°-20°	407.2	18.9
20°-30°	664.9	30.9
30°-40°	651.8	30.3
40°-50°	249.9	11.6
50°-60°	36.6	1.7
60°-70°	5.4	0.3
70°-80°	2.8	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1205.9	56.0
0°-40°	1857.7	86.3
0°-60°	2144.2	99.6
0°-90°	2153.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2153.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1395	
5°	1400	134
15°	1436	407
25°	1454	665
35°	1080	652
45°	299	250
55°	33	37
65°	5	5
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P593178

CATALOG NUMBER: HCC6W25D010MB-HM60525950-61WDBB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1394.8
2.5°	1391.6
5°	1399.7
7.5°	1404.6
10°	1407.9
12.5°	1419.4
15°	1435.7
17.5°	1448.7
20°	1455.2
22.5°	1456.9
25°	1453.6
27.5°	1430.8
30°	1370.4
32.5°	1256.3
35°	1080.0
37.5°	863.1
40°	647.7
42.5°	461.7
45°	298.6
47.5°	182.7
50°	107.6
52.5°	62.0
55°	32.6
57.5°	14.7
60°	8.1
62.5°	6.5
65°	4.9
67.5°	4.9
70°	3.3
72.5°	3.3
75°	3.3
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)