

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582129

Luminaire Tested: **HCC6W30D010MB-HM63040827-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010MB-HM63040827-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2827.1 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582129
CATALOG NUMBER: HCC6W30D010MB-HM63040827-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P582129

CATALOG NUMBER: HCC6W30D010MB-HM63040827-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105244
5°	104859
10°	103104
15°	101289
20°	97793
25°	92727
30°	84342
35°	67392
40°	44970
45°	32050
50°	26711
55°	23273
60°	21994
65°	20716
70°	19026
75°	17771
80°	16132
85°	14152



TEST NUMBER: P582129
 CATALOG NUMBER: HCC6W30D010MB-HM63040827-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.2	6.4
10°-20°	501.1	17.7
20°-30°	700.3	24.8
30°-40°	616.9	21.8
40°-50°	333.3	11.8
50°-60°	222.8	7.9
60°-70°	158.0	5.6
70°-80°	88.7	3.1
80°-90°	25.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1381.6	48.9
0°-40°	1998.5	70.7
0°-60°	2554.5	90.4
0°-90°	2827.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2827.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1920	
5°	1906	180
15°	1785	501
25°	1533	700
35°	1007	617
45°	413	333
55°	244	223
65°	160	158
75°	84	89
85°	22	26
90°	0	



TEST NUMBER: P582129
CATALOG NUMBER: HCC6W30D010MB-HM63040827-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1919.8
2.5°	1909.5
5°	1905.5
7.5°	1887.1
10°	1852.2
12.5°	1819.5
15°	1784.7
17.5°	1737.6
20°	1676.3
22.5°	1608.7
25°	1533.0
27.5°	1445.0
30°	1332.4
32.5°	1193.3
35°	1007.0
37.5°	804.4
40°	628.4
42.5°	495.3
45°	413.4
47.5°	358.1
50°	313.2
52.5°	276.3
55°	243.5
57.5°	221.0
60°	200.6
62.5°	180.1
65°	159.7
67.5°	139.2
70°	118.7
72.5°	100.2
75°	83.9
77.5°	67.5
80°	51.1
82.5°	36.9
85°	22.5
87.5°	10.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)