

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582156

Luminaire Tested: **HCC6S30D010MB-HM63040830-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MB-HM63040830-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3248.2 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582156
CATALOG NUMBER: HCC6S30D010MB-HM63040830-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582156
 CATALOG NUMBER: HCC6S30D010MB-HM63040830-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	83	80		84	81	78	77
4	94	86	79	75	92	85	79	74	82	77	73		80	76	73		78	75	72	70
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61		70	65	61		68	64	60	59
7	79	68	62	57	77	68	61	57	66	60	56		65	60	56		64	59	56	54
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60	55	51	50
9	70	59	53	48	69	59	53	48	58	52	48		57	52	48		56	51	48	46
10	66	56	49	45	65	55	49	45	54	49	45		53	48	45		53	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127216
5°	128059
10°	129540
15°	132203
20°	132942
25°	128802
30°	116847
35°	94997
40°	63061
45°	35097
50°	19684
55°	10924
60°	6019
65°	4566
70°	3158
75°	2309
80°	1389
85°	1321



TEST NUMBER: P582156
 CATALOG NUMBER: HCC6S30D010MB-HM63040830-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.1	6.8
10°-20°	656.8	20.2
20°-30°	968.0	29.8
30°-40°	865.8	26.7
40°-50°	375.6	11.6
50°-60°	110.4	3.4
60°-70°	35.2	1.1
70°-80°	12.4	0.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1847.0	56.9
0°-40°	2712.8	83.5
0°-60°	3198.8	98.5
0°-90°	3248.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3248.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2321	
5°	2327	222
15°	2329	657
25°	2129	968
35°	1420	866
45°	453	376
55°	114	110
65°	35	35
75°	11	12
85°	2	2
90°	0	



TEST NUMBER: P582156

CATALOG NUMBER: HCC6S30D010MB-HM63040830-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2320.6
2.5°	2313.9
5°	2327.1
7.5°	2331.5
10°	2327.1
12.5°	2327.1
15°	2329.4
17.5°	2316.2
20°	2278.8
22.5°	2215.1
25°	2129.4
27.5°	2008.5
30°	1845.9
32.5°	1652.5
35°	1419.5
37.5°	1153.7
40°	881.2
42.5°	643.8
45°	452.7
47.5°	323.1
50°	230.8
52.5°	164.8
55°	114.3
57.5°	76.9
60°	54.9
62.5°	44.0
65°	35.2
67.5°	26.4
70°	19.7
72.5°	15.3
75°	10.9
77.5°	8.8
80°	4.4
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)