

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582166

Luminaire Tested: **HCC6W30D010MW-HM63040835-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582166
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010MW-HM63040835-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3471.2 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582166
CATALOG NUMBER: HCC6W30D010MW-HM63040835-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582166
 CATALOG NUMBER: HCC6W30D010MW-HM63040835-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207297
5°	207715
10°	211129
15°	212674
20°	194407
25°	152767
30°	111821
35°	79324
40°	37513
45°	14319
50°	6422
55°	1739
60°	757
65°	584
70°	369
75°	487
80°	0
85°	0



TEST NUMBER: P582166
 CATALOG NUMBER: HCC6W30D010MW-HM63040835-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.1	10.4
10°-20°	1035.7	29.8
20°-30°	1152.1	33.2
30°-40°	719.7	20.7
40°-50°	171.0	4.9
50°-60°	24.5	0.7
60°-70°	5.1	0.1
70°-80°	2.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2548.8	73.4
0°-40°	3268.5	94.2
0°-60°	3464.0	99.8
0°-90°	3471.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3471.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3781	
5°	3775	361
15°	3747	1036
25°	2526	1152
35°	1185	720
45°	185	171
55°	18	24
65°	4	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582166
CATALOG NUMBER: HCC6W30D010MW-HM63040835-61NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	3781.4
2.5°	3765.4
5°	3774.6
7.5°	3788.3
10°	3792.8
12.5°	3790.5
15°	3747.3
17.5°	3601.4
20°	3332.4
22.5°	2954.1
25°	2525.6
27.5°	2115.2
30°	1766.5
32.5°	1477.0
35°	1185.3
37.5°	870.7
40°	524.2
42.5°	303.2
45°	184.7
47.5°	118.5
50°	75.3
52.5°	43.3
55°	18.2
57.5°	9.2
60°	6.9
62.5°	6.9
65°	4.5
67.5°	4.5
70°	2.3
72.5°	2.3
75°	2.3
77.5°	2.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)