

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582163

Luminaire Tested: **HCC6W30D010SL-HM63040835-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582163
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010SL-HM63040835-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3594.3 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582163
CATALOG NUMBER: HCC6W30D010SL-HM63040835-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P582163

CATALOG NUMBER: HCC6W30D010SL-HM63040835-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70	66	62	61
8	79	70	63	59	78	69	63	59	68	63	59		67	62	59		66	62	58	57
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62	58	55	54
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	170677
5°	173338
10°	183213
15°	203991
20°	211553
25°	173568
30°	121626
35°	82978
40°	43224
45°	15203
50°	6806
55°	2179
60°	1250
65°	895
70°	721
75°	487
80°	0
85°	0



TEST NUMBER: P582163
 CATALOG NUMBER: HCC6W30D010SL-HM63040835-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.1	8.5
10°-20°	1010.9	28.1
20°-30°	1287.1	35.8
30°-40°	767.1	21.3
40°-50°	186.0	5.2
50°-60°	28.6	0.8
60°-70°	7.0	0.2
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2603.1	72.4
0°-40°	3370.2	93.8
0°-60°	3584.8	99.7
0°-90°	3594.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3594.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3113	
5°	3150	305
15°	3594	1011
25°	2870	1287
35°	1240	767
45°	196	186
55°	23	29
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582163
CATALOG NUMBER: HCC6W30D010SL-HM63040835-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3113.4
2.5°	3113.4
5°	3149.9
7.5°	3206.9
10°	3291.3
12.5°	3423.5
15°	3594.3
17.5°	3701.5
20°	3626.3
22.5°	3336.8
25°	2869.5
27.5°	2354.5
30°	1921.4
32.5°	1570.4
35°	1239.9
37.5°	914.0
40°	604.0
42.5°	325.9
45°	196.1
47.5°	123.1
50°	79.8
52.5°	47.9
55°	22.8
57.5°	13.7
60°	11.4
62.5°	9.2
65°	6.9
67.5°	4.5
70°	4.5
72.5°	2.3
75°	2.3
77.5°	2.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)