

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582165

Luminaire Tested: **HCC6S30D010MW-HM63040835-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582165
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MW-HM63040835-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3147.5 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582165
CATALOG NUMBER: HCC6S30D010MW-HM63040835-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P582165

CATALOG NUMBER: HCC6S30D010MW-HM63040835-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79				
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70				
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63				
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57				
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52				
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48				
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44				
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40				
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117167
5°	116740
10°	114789
15°	112765
20°	108865
25°	103234
30°	93901
35°	75027
40°	50058
45°	35686
50°	29730
55°	25920
60°	24483
65°	23063
70°	21189
75°	19804
80°	17995
85°	15788



TEST NUMBER: P582165
 CATALOG NUMBER: HCC6S30D010MW-HM63040835-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.6	6.4
10°-20°	557.9	17.7
20°-30°	779.6	24.8
30°-40°	686.7	21.8
40°-50°	371.0	11.8
50°-60°	248.1	7.9
60°-70°	175.8	5.6
70°-80°	98.8	3.1
80°-90°	28.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1538.1	48.9
0°-40°	2224.9	70.7
0°-60°	2844.0	90.4
0°-90°	3147.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3147.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2137	
5°	2121	201
15°	1987	558
25°	1707	780
35°	1121	687
45°	460	371
55°	271	248
65°	178	176
75°	94	99
85°	25	29
90°	0	



TEST NUMBER: P582165
CATALOG NUMBER: HCC6S30D010MW-HM63040835-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2137.3
2.5°	2125.9
5°	2121.4
7.5°	2100.8
10°	2062.1
12.5°	2025.7
15°	1986.9
17.5°	1934.5
20°	1866.1
22.5°	1791.0
25°	1706.7
27.5°	1608.7
30°	1483.4
32.5°	1328.5
35°	1121.1
37.5°	895.4
40°	699.5
42.5°	551.5
45°	460.3
47.5°	398.8
50°	348.6
52.5°	307.6
55°	271.2
57.5°	246.1
60°	223.3
62.5°	200.5
65°	177.8
67.5°	154.9
70°	132.2
72.5°	111.6
75°	93.5
77.5°	75.1
80°	57.0
82.5°	41.0
85°	25.1
87.5°	11.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)