

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593203

Luminaire Tested: **HCC6S30D010MW-HM63040850-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593203
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MW-HM63040850-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3647.1 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593203
CATALOG NUMBER: HCC6S30D010MW-HM63040850-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P593203

CATALOG NUMBER: HCC6S30D010MW-HM63040850-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94	94	94	94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76	76	76	76
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71	71	71	71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67	67	67	67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217811
5°	218247
10°	221840
15°	223458
20°	204266
25°	160509
30°	117486
35°	83346
40°	39424
45°	15040
50°	6746
55°	1826
60°	778
65°	623
70°	385
75°	508
80°	0
85°	0



TEST NUMBER: P593203
 CATALOG NUMBER: HCC6S30D010MW-HM63040850-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.4	10.4
10°-20°	1088.2	29.8
20°-30°	1210.5	33.2
30°-40°	756.2	20.7
40°-50°	179.7	4.9
50°-60°	25.7	0.7
60°-70°	5.3	0.1
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2678.1	73.4
0°-40°	3434.3	94.2
0°-60°	3639.6	99.8
0°-90°	3647.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3647.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3973	
5°	3966	379
15°	3937	1088
25°	2654	1210
35°	1245	756
45°	194	180
55°	19	26
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P593203
CATALOG NUMBER: HCC6S30D010MW-HM63040850-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3973.2
2.5°	3956.4
5°	3966.0
7.5°	3980.4
10°	3985.2
12.5°	3982.8
15°	3937.3
17.5°	3784.0
20°	3501.4
22.5°	3103.9
25°	2653.6
27.5°	2222.5
30°	1856.0
32.5°	1551.9
35°	1245.4
37.5°	914.8
40°	550.9
42.5°	318.5
45°	194.0
47.5°	124.5
50°	79.1
52.5°	45.5
55°	19.1
57.5°	9.6
60°	7.1
62.5°	7.1
65°	4.8
67.5°	4.8
70°	2.4
72.5°	2.4
75°	2.4
77.5°	2.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)