

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582210

Luminaire Tested: **HCC6S30D010BZ-HM63040927-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010BZ-HM63040927-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2556.6 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582210
CATALOG NUMBER: HCC6S30D010BZ-HM63040927-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582210

CATALOG NUMBER: HCC6S30D010BZ-HM63040927-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59		
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50		
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100124
5°	100787
10°	101952
15°	104047
20°	104630
25°	101371
30°	91964
35°	74773
40°	49629
45°	27623
50°	15488
55°	8592
60°	4747
65°	3593
70°	2500
75°	1843
80°	1073
85°	1132



TEST NUMBER: P582210
 CATALOG NUMBER: HCC6S30D010BZ-HM63040927-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.8	6.8
10°-20°	516.9	20.2
20°-30°	761.9	29.8
30°-40°	681.5	26.7
40°-50°	295.6	11.6
50°-60°	86.9	3.4
60°-70°	27.8	1.1
70°-80°	9.8	0.4
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1453.6	56.9
0°-40°	2135.1	83.5
0°-60°	2517.6	98.5
0°-90°	2556.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2556.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1826	
5°	1832	175
15°	1833	517
25°	1676	762
35°	1117	681
45°	356	296
55°	90	87
65°	28	28
75°	9	10
85°	2	1
90°	0	



TEST NUMBER: P582210
CATALOG NUMBER: HCC6S30D010BZ-HM63040927-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1826.4
2.5°	1821.2
5°	1831.5
7.5°	1835.0
10°	1831.5
12.5°	1831.5
15°	1833.3
17.5°	1823.0
20°	1793.5
22.5°	1743.4
25°	1675.9
27.5°	1580.8
30°	1452.8
32.5°	1300.6
35°	1117.3
37.5°	908.0
40°	693.5
42.5°	506.8
45°	356.3
47.5°	254.2
50°	181.6
52.5°	129.7
55°	89.9
57.5°	60.5
60°	43.3
62.5°	34.6
65°	27.7
67.5°	20.8
70°	15.6
72.5°	12.1
75°	8.7
77.5°	6.9
80°	3.4
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)