

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582211

Luminaire Tested: **HCC6S30D010MB-HM63040927-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MB-HM63040927-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2523.7 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582211
CATALOG NUMBER: HCC6S30D010MB-HM63040927-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P582211

CATALOG NUMBER: HCC6S30D010MB-HM63040927-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86122
5°	86066
10°	85236
15°	84348
20°	81965
25°	78507
30°	72866
35°	62687
40°	45757
45°	31352
50°	25210
55°	21963
60°	20272
65°	19276
70°	18016
75°	16839
80°	15280
85°	13020



TEST NUMBER: P582211
 CATALOG NUMBER: HCC6S30D010MB-HM63040927-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	5.9
10°-20°	417.4	16.5
20°-30°	593.7	23.5
30°-40°	571.6	22.6
40°-50°	328.8	13.0
50°-60°	208.3	8.3
60°-70°	147.5	5.8
70°-80°	84.1	3.3
80°-90°	24.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1159.3	45.9
0°-40°	1730.9	68.6
0°-60°	2268.1	89.9
0°-90°	2523.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2523.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1571	
5°	1564	148
15°	1486	417
25°	1298	594
35°	937	572
45°	404	329
55°	230	208
65°	149	148
75°	80	84
85°	21	24
90°	0	



TEST NUMBER: P582211
CATALOG NUMBER: HCC6S30D010MB-HM63040927-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1571.0
2.5°	1564.0
5°	1564.0
7.5°	1553.7
10°	1531.2
12.5°	1508.7
15°	1486.2
17.5°	1451.8
20°	1405.0
22.5°	1353.2
25°	1297.9
27.5°	1230.5
30°	1151.1
32.5°	1054.3
35°	936.7
37.5°	793.3
40°	639.4
42.5°	504.6
45°	404.4
47.5°	340.4
50°	295.6
52.5°	259.2
55°	229.8
57.5°	203.9
60°	184.9
62.5°	167.6
65°	148.6
67.5°	131.4
70°	112.4
72.5°	95.0
75°	79.5
77.5°	64.0
80°	48.4
82.5°	34.6
85°	20.7
87.5°	8.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)