

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582205

Luminaire Tested: **HCC6S30D010MW-HM63040927-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MW-HM63040927-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2447.7 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582205
CATALOG NUMBER: HCC6S30D010MW-HM63040927-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582205
 CATALOG NUMBER: HCC6S30D010MW-HM63040927-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43				
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39				
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87488
5°	87244
10°	85943
15°	84586
20°	81802
25°	77908
30°	71138
35°	57273
40°	38601
45°	28150
50°	24323
55°	21982
60°	20854
65°	19743
70°	18561
75°	17580
80°	16353
85°	15284



TEST NUMBER: P582205
 CATALOG NUMBER: HCC6S30D010MW-HM63040927-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.1	6.1
10°-20°	418.5	17.1
20°-30°	588.0	24.0
30°-40°	523.4	21.4
40°-50°	292.5	12.0
50°-60°	208.4	8.5
60°-70°	151.6	6.2
70°-80°	87.8	3.6
80°-90°	27.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1156.6	47.3
0°-40°	1680.0	68.6
0°-60°	2181.0	89.1
0°-90°	2447.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2447.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1596	
5°	1585	150
15°	1490	419
25°	1288	588
35°	856	523
45°	363	293
55°	230	208
65°	152	152
75°	83	88
85°	24	27
90°	0	



TEST NUMBER: P582205
CATALOG NUMBER: HCC6S30D010MW-HM63040927-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1595.9
2.5°	1589.0
5°	1585.4
7.5°	1571.6
10°	1543.9
12.5°	1518.0
15°	1490.4
17.5°	1452.4
20°	1402.2
22.5°	1346.9
25°	1288.0
27.5°	1215.5
30°	1123.8
32.5°	1006.3
35°	855.8
37.5°	686.4
40°	539.4
42.5°	430.5
45°	363.1
47.5°	318.2
50°	285.2
52.5°	255.9
55°	230.0
57.5°	209.3
60°	190.2
62.5°	172.9
65°	152.2
67.5°	134.8
70°	115.8
72.5°	98.6
75°	83.0
77.5°	67.4
80°	51.8
82.5°	38.0
85°	24.3
87.5°	12.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)