

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582222

Luminaire Tested: **HCC6S30D010SL-HM63040930-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582222
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010SL-HM63040930-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2810.0 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582222
CATALOG NUMBER: HCC6S30D010SL-HM63040930-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582222
 CATALOG NUMBER: HCC6S30D010SL-HM63040930-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79	79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70	70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63	63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57	57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52	52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44	44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41	41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106433
5°	105932
10°	103589
15°	101158
20°	97361
25°	92074
30°	83671
35°	67733
40°	45678
45°	31391
50°	25713
55°	22499
60°	21292
65°	20093
70°	18865
75°	17940
80°	16290
85°	14278



TEST NUMBER: P582222
 CATALOG NUMBER: HCC6S30D010SL-HM63040930-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.7	6.5
10°-20°	500.6	17.8
20°-30°	695.4	24.7
30°-40°	619.2	22.0
40°-50°	328.7	11.7
50°-60°	214.9	7.6
60°-70°	154.0	5.5
70°-80°	89.3	3.2
80°-90°	26.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1377.7	49.0
0°-40°	1996.9	71.1
0°-60°	2540.5	90.4
0°-90°	2810.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2810.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1942	
5°	1925	182
15°	1782	501
25°	1522	695
35°	1012	619
45°	405	329
55°	235	215
65°	155	154
75°	85	89
85°	23	26
90°	0	



TEST NUMBER: P582222
CATALOG NUMBER: HCC6S30D010SL-HM63040930-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1941.5
2.5°	1931.2
5°	1925.0
7.5°	1902.3
10°	1860.9
12.5°	1823.8
15°	1782.4
17.5°	1730.8
20°	1668.9
22.5°	1598.6
25°	1522.2
27.5°	1433.3
30°	1321.8
32.5°	1187.6
35°	1012.1
37.5°	817.9
40°	638.3
42.5°	495.7
45°	404.9
47.5°	344.9
50°	301.5
52.5°	266.5
55°	235.4
57.5°	212.7
60°	194.2
62.5°	175.6
65°	154.9
67.5°	136.3
70°	117.7
72.5°	101.2
75°	84.7
77.5°	68.1
80°	51.6
82.5°	37.2
85°	22.7
87.5°	10.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)