

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582230

Luminaire Tested: **HCC6W30D010BZ-HM63040930-61WDWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582230
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010BZ-HM63040930-61WDWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3247.8 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582230
CATALOG NUMBER: HCC6W30D010BZ-HM63040930-61WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P582230
 CATALOG NUMBER: HCC6W30D010BZ-HM63040930-61WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91				
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82				
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69				
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63				
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58				
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54				
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50				
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46				
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121131
5°	122166
10°	126562
15°	137475
20°	142999
25°	136774
30°	118037
35°	84992
40°	47883
45°	24817
50°	14797
55°	10657
60°	9056
65°	10442
70°	13239
75°	14001
80°	13701
85°	13020



TEST NUMBER: P582230
 CATALOG NUMBER: HCC6W30D010BZ-HM63040930-61WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.6	6.6
10°-20°	683.2	21.0
20°-30°	1021.2	31.4
30°-40°	780.6	24.0
40°-50°	272.7	8.4
50°-60°	103.9	3.2
60°-70°	81.5	2.5
70°-80°	69.0	2.1
80°-90°	22.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1918.0	59.1
0°-40°	2698.6	83.1
0°-60°	3075.1	94.7
0°-90°	3247.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3247.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2210	
5°	2220	214
15°	2422	683
25°	2261	1021
35°	1270	781
45°	320	273
55°	112	104
65°	80	81
75°	66	69
85°	21	22
90°	0	



TEST NUMBER: P582230
CATALOG NUMBER: HCC6W30D010BZ-HM63040930-61WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2209.6
2.5°	2203.5
5°	2220.0
7.5°	2242.7
10°	2273.6
12.5°	2343.9
15°	2422.3
17.5°	2469.8
20°	2451.2
22.5°	2376.9
25°	2261.2
27.5°	2096.0
30°	1864.7
32.5°	1588.0
35°	1270.0
37.5°	941.7
40°	669.1
42.5°	468.8
45°	320.1
47.5°	225.1
50°	173.5
52.5°	136.3
55°	111.5
57.5°	90.8
60°	82.6
62.5°	80.5
65°	80.5
67.5°	84.7
70°	82.6
72.5°	76.5
75°	66.1
77.5°	55.8
80°	43.4
82.5°	31.0
85°	20.7
87.5°	8.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)