

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582241

Luminaire Tested: **HCC6W30D010SL-HM63040935-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582241
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010SL-HM63040935-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2882.7 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582241
CATALOG NUMBER: HCC6W30D010SL-HM63040935-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582241

CATALOG NUMBER: HCC6W30D010SL-HM63040935-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				46
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43				43
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39				39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36				36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103035
5°	102751
10°	101217
15°	99620
20°	96340
25°	91759
30°	83785
35°	67452
40°	45464
45°	33151
50°	28656
55°	25892
60°	24559
65°	23245
70°	21863
75°	20694
80°	19289
85°	17926



TEST NUMBER: P582241
 CATALOG NUMBER: HCC6W30D010SL-HM63040935-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.7	6.1
10°-20°	492.9	17.1
20°-30°	692.5	24.0
30°-40°	616.5	21.4
40°-50°	344.5	12.0
50°-60°	245.5	8.5
60°-70°	178.6	6.2
70°-80°	103.3	3.6
80°-90°	32.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1362.2	47.3
0°-40°	1978.6	68.6
0°-60°	2568.6	89.1
0°-90°	2882.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2882.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1880	
5°	1867	177
15°	1755	493
25°	1517	693
35°	1008	616
45°	428	344
55°	271	245
65°	179	179
75°	98	103
85°	28	32
90°	0	



TEST NUMBER: P582241
CATALOG NUMBER: HCC6W30D010SL-HM63040935-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1879.5
2.5°	1871.4
5°	1867.2
7.5°	1850.9
10°	1818.3
12.5°	1787.9
15°	1755.3
17.5°	1710.5
20°	1651.4
22.5°	1586.2
25°	1517.0
27.5°	1431.6
30°	1323.6
32.5°	1185.1
35°	1007.9
37.5°	808.4
40°	635.3
42.5°	507.0
45°	427.6
47.5°	374.7
50°	336.0
52.5°	301.4
55°	270.9
57.5°	246.4
60°	224.0
62.5°	203.7
65°	179.2
67.5°	158.9
70°	136.4
72.5°	116.0
75°	97.7
77.5°	79.4
80°	61.1
82.5°	44.8
85°	28.5
87.5°	14.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)