

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582263

Luminaire Tested: **HCC6S30D010MB-HM63040940-61WDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MB-HM63040940-61WDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3368.3 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582263
CATALOG NUMBER: HCC6S30D010MB-HM63040940-61WDC

Luminous Intensity Polar Plot





TEST NUMBER: P582263
 CATALOG NUMBER: HCC6S30D010MB-HM63040940-61WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78			78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52			52
9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48			48
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119420
5°	121021
10°	125554
15°	136544
20°	152666
25°	160691
30°	141458
35°	98123
40°	58588
45°	27848
50°	10507
55°	4387
60°	1371
65°	1077
70°	673
75°	445
80°	663
85°	0



TEST NUMBER: P582263
 CATALOG NUMBER: HCC6S30D010MB-HM63040940-61WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.7	6.3
10°-20°	690.9	20.5
20°-30°	1183.8	35.1
30°-40°	919.4	27.3
40°-50°	303.9	9.0
50°-60°	46.6	1.4
60°-70°	8.2	0.2
70°-80°	3.0	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2086.3	61.9
0°-40°	3005.7	89.2
0°-60°	3356.2	99.6
0°-90°	3368.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3368.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2178	
5°	2199	212
15°	2406	691
25°	2657	1184
35°	1466	919
45°	359	304
55°	46	47
65°	8	8
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P582263
CATALOG NUMBER: HCC6S30D010MB-HM63040940-61WDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2178.4
2.5°	2176.2
5°	2199.2
7.5°	2224.3
10°	2255.5
12.5°	2318.2
15°	2405.9
17.5°	2512.5
20°	2616.9
22.5°	2677.5
25°	2656.6
27.5°	2512.5
30°	2234.7
32.5°	1860.9
35°	1466.2
37.5°	1113.1
40°	818.7
42.5°	578.6
45°	359.2
47.5°	200.5
50°	123.2
52.5°	75.1
55°	45.9
57.5°	22.9
60°	12.5
62.5°	10.5
65°	8.3
67.5°	6.3
70°	4.2
72.5°	4.2
75°	2.1
77.5°	2.1
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)