

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593225

Luminaire Tested: **HCC6S30D010BZ-HM63040950-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010BZ-HM63040950-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2956.9 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593225
CATALOG NUMBER: HCC6S30D010BZ-HM63040950-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P593225
 CATALOG NUMBER: HCC6S30D010BZ-HM63040950-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90		88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80		78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71		69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64		62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58		56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53		51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48		46
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44		43
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41		39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38		36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105693
5°	105404
10°	103834
15°	102186
20°	98825
25°	94130
30°	85944
35°	69198
40°	46637
45°	34004
50°	29398
55°	26551
60°	25184
65°	23842
70°	22424
75°	21223
80°	19794
85°	18367



TEST NUMBER: P593225
 CATALOG NUMBER: HCC6S30D010BZ-HM63040950-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.3	6.1
10°-20°	505.6	17.1
20°-30°	710.4	24.0
30°-40°	632.3	21.4
40°-50°	353.4	12.0
50°-60°	251.8	8.5
60°-70°	183.2	6.2
70°-80°	106.0	3.6
80°-90°	32.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1397.3	47.3
0°-40°	2029.6	68.6
0°-60°	2634.8	89.1
0°-90°	2956.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2956.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1928	
5°	1915	181
15°	1800	506
25°	1556	710
35°	1034	632
45°	439	353
55°	278	252
65°	184	183
75°	100	106
85°	29	33
90°	0	



TEST NUMBER: P593225
CATALOG NUMBER: HCC6S30D010BZ-HM63040950-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1928.0
2.5°	1919.5
5°	1915.4
7.5°	1898.7
10°	1865.3
12.5°	1833.9
15°	1800.5
17.5°	1754.6
20°	1694.0
22.5°	1627.1
25°	1556.2
27.5°	1468.4
30°	1357.7
32.5°	1215.6
35°	1034.0
37.5°	829.2
40°	651.7
42.5°	520.1
45°	438.6
47.5°	384.3
50°	344.7
52.5°	309.1
55°	277.8
57.5°	252.8
60°	229.7
62.5°	208.9
65°	183.8
67.5°	162.9
70°	139.9
72.5°	119.0
75°	100.2
77.5°	81.4
80°	62.7
82.5°	45.9
85°	29.2
87.5°	14.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)