

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593224

Luminaire Tested: **HCC6W30D010MW-HM63040950-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593224
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010MW-HM63040950-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2842.1 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593224
CATALOG NUMBER: HCC6W30D010MW-HM63040950-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P593224
 CATALOG NUMBER: HCC6W30D010MW-HM63040950-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107645
5°	107143
10°	104774
15°	102316
20°	98469
25°	93126
30°	84627
35°	68502
40°	46194
45°	31747
50°	26012
55°	22766
60°	21533
65°	20326
70°	19074
75°	18131
80°	16479
85°	14404



TEST NUMBER: P593224
 CATALOG NUMBER: HCC6W30D010MW-HM63040950-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	6.5
10°-20°	506.3	17.8
20°-30°	703.4	24.7
30°-40°	626.2	22.0
40°-50°	332.5	11.7
50°-60°	217.4	7.6
60°-70°	155.8	5.5
70°-80°	90.4	3.2
80°-90°	26.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1393.4	49.0
0°-40°	2019.7	71.1
0°-60°	2569.5	90.4
0°-90°	2842.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2842.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1964	
5°	1947	184
15°	1803	506
25°	1540	703
35°	1024	626
45°	410	332
55°	238	217
65°	157	156
75°	86	90
85°	23	26
90°	0	



TEST NUMBER: P593224
CATALOG NUMBER: HCC6W30D010MW-HM63040950-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1963.6
2.5°	1953.2
5°	1947.0
7.5°	1923.9
10°	1882.2
12.5°	1844.6
15°	1802.8
17.5°	1750.6
20°	1687.9
22.5°	1616.9
25°	1539.6
27.5°	1449.7
30°	1336.9
32.5°	1201.1
35°	1023.6
37.5°	827.2
40°	645.5
42.5°	501.4
45°	409.5
47.5°	348.9
50°	305.0
52.5°	269.4
55°	238.2
57.5°	215.2
60°	196.4
62.5°	177.5
65°	156.7
67.5°	137.9
70°	119.0
72.5°	102.4
75°	85.6
77.5°	69.0
80°	52.2
82.5°	37.6
85°	22.9
87.5°	10.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)