

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582283

Luminaire Tested: **HCC6S35D010BZ-HM63040827-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010BZ-HM63040827-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3551.2 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582283
CATALOG NUMBER: HCC6S35D010BZ-HM63040827-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P582283
 CATALOG NUMBER: HCC6S35D010BZ-HM63040827-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78				
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69				
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56				
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51				
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42				
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39				
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121185
5°	121109
10°	119938
15°	118695
20°	115341
25°	110474
30°	102528
35°	88211
40°	64392
45°	44113
50°	35462
55°	30919
60°	28528
65°	27124
70°	25341
75°	23701
80°	21467
85°	18367



TEST NUMBER: P582283
 CATALOG NUMBER: HCC6S35D010BZ-HM63040827-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.6	5.9
10°-20°	587.4	16.5
20°-30°	835.4	23.5
30°-40°	804.3	22.6
40°-50°	462.7	13.0
50°-60°	293.2	8.3
60°-70°	207.6	5.8
70°-80°	118.3	3.3
80°-90°	33.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1631.4	45.9
0°-40°	2435.6	68.6
0°-60°	3191.6	89.9
0°-90°	3551.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3551.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2211	
5°	2201	209
15°	2091	587
25°	1826	835
35°	1318	804
45°	569	463
55°	324	293
65°	209	208
75°	112	118
85°	29	34
90°	0	



TEST NUMBER: P582283
CATALOG NUMBER: HCC6S35D010BZ-HM63040827-61WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2210.6
2.5°	2200.8
5°	2200.8
7.5°	2186.3
10°	2154.6
12.5°	2123.0
15°	2091.4
17.5°	2042.8
20°	1977.1
22.5°	1904.2
25°	1826.4
27.5°	1731.5
30°	1619.7
32.5°	1483.5
35°	1318.1
37.5°	1116.2
40°	899.8
42.5°	710.1
45°	569.0
47.5°	479.1
50°	415.8
52.5°	364.8
55°	323.5
57.5°	287.0
60°	260.2
62.5°	235.9
65°	209.1
67.5°	184.9
70°	158.1
72.5°	133.7
75°	111.9
77.5°	90.0
80°	68.0
82.5°	48.7
85°	29.2
87.5°	12.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)