

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582300

Luminaire Tested: **HCC6W35D010MW-HM63040830-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582300
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010MW-HM63040830-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3859.3 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582300
CATALOG NUMBER: HCC6W35D010MW-HM63040830-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582300
 CATALOG NUMBER: HCC6W35D010MW-HM63040830-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84			84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77			77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59			59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54			54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50			50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151150
5°	152157
10°	153916
15°	157067
20°	157957
25°	153027
30°	138825
35°	112879
40°	74919
45°	41702
50°	23377
55°	12970
60°	7149
65°	5422
70°	3767
75°	2775
80°	1673
85°	1635



TEST NUMBER: P582300
 CATALOG NUMBER: HCC6W35D010MW-HM63040830-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.9	6.8
10°-20°	780.4	20.2
20°-30°	1150.2	29.8
30°-40°	1028.7	26.7
40°-50°	446.3	11.6
50°-60°	131.1	3.4
60°-70°	41.8	1.1
70°-80°	14.8	0.4
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2194.4	56.9
0°-40°	3223.2	83.5
0°-60°	3800.6	98.5
0°-90°	3859.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3859.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2757	
5°	2765	264
15°	2768	780
25°	2530	1150
35°	1687	1029
45°	538	446
55°	136	131
65°	42	42
75°	13	15
85°	3	2
90°	0	



TEST NUMBER: P582300
CATALOG NUMBER: HCC6W35D010MW-HM63040830-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2757.2
2.5°	2749.3
5°	2765.0
7.5°	2770.2
10°	2765.0
12.5°	2765.0
15°	2767.5
17.5°	2751.9
20°	2707.6
22.5°	2631.8
25°	2529.9
27.5°	2386.4
30°	2193.1
32.5°	1963.4
35°	1686.7
37.5°	1370.8
40°	1046.9
42.5°	765.0
45°	537.9
47.5°	383.8
50°	274.1
52.5°	195.8
55°	135.7
57.5°	91.4
60°	65.2
62.5°	52.2
65°	41.8
67.5°	31.3
70°	23.5
72.5°	18.3
75°	13.1
77.5°	10.4
80°	5.3
82.5°	2.6
85°	2.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)